




Low profile transformer FLN 24/9

Electrical data	
Type	FLN 24/9
Input	
Rated input Voltage	2 x 115 Vac
Rated frequency	50 - 60 Hz
Output	
Rated output voltage	2 x 9 Vac
Rated Power	24.0 VA
No-load voltage (app. x factor)	1.26
No-load loss (typ.)	2.00 W
Efficiency	74 %
Standards	
Classification	Safety isolating transformer
Approvals	
Approvals	cURus, ENEC 10 (VDE)
Environment	
Ambient temperature max.	70 °C
Safety and protection	
Type	encapsulated
Class of Insulation System	B
Protection index	IP 00
Safety class (prepared)	II
Short circuit strength	non-short-circuit proof
Order numbers	
Order Number	FLN 24/9

Mechanical data	
Type	FLN 24/9
Terminal and mounting	
Terminals	Pins for printed circuit boards
Measures and weights	
Core type	UI 39/17
Weight	0.49 kg



Subjects to change.