

Shock-Safe Fuseholder, 4.7 x 16 mm, Fingerrip, Rear-Side



250 VAC · 1 W/5A



GAM  
T1 NNO

### Description

- Screw type fuse carrier

### References

Fuseholder to D0

### Weblinks



pdf-datasheet, html-datasheet, General Product Information, Approvals, CE declaration of conformity, RoHS, CHINA-RoHS, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check, Detailed request for product

### Technical Data

Fuse-Link	4.7 x 16mm
Mounting	Panel Mount, Rear Side
Mounting	Fixing Nut
Terminal	Solder
Rated Voltage	250 VAC
Rated current	5A
Rated Power Acceptance IEC	1 W / 5 A @ Ta 23 °C
Degree of Protection	IP 67
Protection Class	Suitable for appliances with protection class I or II acc. to IEC 61140
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/21 acc. to IEC 60068-1
Material: Socket	Thermoset, black
Unit Weight (Socket/Cap)	8.2 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	Type

Soldering Methods	Iron
Resistance to Vibration	acc. to NF C 20-706 / IEC 60068-2-6, test Fc
Shocks	acc. to NF C 20-706 / IEC 60068-2-27
Bumps	acc. to NF C 20-729 / IEC 60068-2-29
Salt Mist	acc. to NF C 20-711 / IEC 60068-2-11
Dump Heat	acc. to NF C 20-604
Climatic Composite	acc. to NF C 20-619 Phase D
Admissible Torque on Fixing Nut	max 0.7 Nm
Panel Thickness s	max 2 mm

### Dimension



Mounting holes

### All Variants

	Cap	Degree of Protection	Order Number
●	Fingerrip	IP 67	7090.6020

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging Unit**    Bulk (10 pcs.)

---