

Case set with 4 RUKO mini-boxes for metalworking in plastic case

Set of tungsten carbide rotary burrs in mini-box



1x Ø 10,0 mm shape A, cylinder (ZYA) with end toothing
 1x Ø 10,0 mm shape G, tree (SPG)
 1x Ø 10,0 mm shape D, ball (KUD)

Art.-No. 116 001




Taper and deburring countersinker set HSS, CBN ground in mini-box



6-piece set of taper and deburring countersinker
 DIN 335 Form C 90°
 Ø 6,3 - 8,3 - 10,4 - 12,4 - 16,5 - 20,5 mm

Art.-No. A 102 156


Machine tap set DIN 371 HSS, in mini-box



10-piece set of machine taps
 M DIN 371 HSS, ground
 each 1x type B - M 4 - M 5 - M 6 - M 8 - M 10
 each 1x type C - M 4 - M 5 - M 6 - M 8 - M 10

Art.-No. A 245 055

Step drill set HSS, spiral fluted, CBN ground, in mini-box



3-piece set of step drills
 Sizes 0/9, 1 and 2
 Ø 4,0 - 12,0 / Ø 4,0 - 20,0 / Ø 4,0 - 30,0 mm

Art.-No. A 101 032

ProCoil Thread repairing assortment in steel case

Assortment M 5 - M12

- 5 twist drills HSS Ø 5,2 - 6,2 - 8,3 - 10,3 - 12,4 mm
- + 5 single-cut taps DIN 352 HSS M 5 - M 6 - M 8 - M 10 - M 12
- + 5 fitting tools M 5 - M 6 - M 8 - M 10 - M 12
- + 5 pin-breakers Ø 3,5 - 4,8 - 6,0 - 7,5 - 9,5 mm
- + 20 inserts M 5 - M 10: Height = 1,0 x Ø
- + 5 inserts M 12: Height = 1,0 x Ø

Assortment M 6 - M14

- 5 twist drills HSS Ø 6,2 - 8,3 - 10,3 - 12,4 - 14,5 mm
- + 5 single-cut taps DIN 352 HSS M 6 - M 8 - M 10 - M 12 - M 14
- + 5 fitting tools M 6 - M 8 - M 10 - M 12 - M 14
- + 5 pin-breakers Ø 4,8 - 6,0 - 7,5 - 9,5 - 11,2 mm
- + 20 inserts M 6 - M 12: Height = 1,0 x Ø
- + 5 inserts M 14: Height = 1,0 x Ø



45 tlg./pcs.

