

Part # 20 PE, 20 AWG Plain Enamel Consolidated Magnet Wire (PE)

Product Construction

Construction 20 AWG (PE):

- Solid bare copper conductor
- Polyurethane / Polyamide (Nylon)
- (PE) Plain Enamel Magnet Wire
- Solderable: 20 AWG at 430°C

Characteristics:

- Temperature: 20 AWG -30°C to +130°C
- MIL JW-1177/9, MW 28-C, Class 130
- RoHS Compliant

Packing:

- 1/4 lb. spools
- 1/2 lb. spools
- 1 lb. spools
- Also available on bulk spools

Sold in standard packages of five spools per gauge size and spool put-up.



Specifications

Conductor Size	20 Plain Enamel Wire AWG
Nominal Diameter in. (mm)	0.0334 in. (0.8484 mm)
Circular Mil. Area	1024.0
Spool Put-Up	1/4 lbs 1/2 lbs 1 lbs
Temperature	-30 to +130 °C