


PRODUCT RANGE							
TYPE	I(Amps) @40°C	L(mH)	CX	CY	R mΩHM	RB kΩHM	TERMINALS
SDC013	1.5	20.0	0.33μF	2x4700pF	205	---	SOLDER LUGS
SDC021	2.0	3.0	0.10μF	2x4700pF	50	470	SOLDER LUGS
SDC051	5.0	2.0	0.10μF	2x4700pF	21	470	SOLDER LUGS
SDC101	10.0	1.5	0.10μF	2x4700pF	13	470	6.3mm TAGS
SDC151	15.0	1.0	0.10μF	2x4700pF	8.6	470	6.3mm TAGS
SDC154	15.0	1.0	0.47μF	2x4700pF	9.1	---	6.3mm TAGS
SDC256	25.0	1.0	0.68μF	2x4700pF	4.8	1000	M5 STUD

DIMENSION (mm)									
TYPE	A	B	C	D	E	F	G	H	J
SDC013	45.0	38.1	M8x9	6	7.5	7.5	7.5	4	7.5
SDC021	45.0	38.1	M8x9	6	7.5	7.5	7.5	4	7.5
SDC051	45.0	38.1	M8x9	6	7.5	7.5	7.5	4	7.5
SDC101	51.0	51.0	M10x12	12	10	15	5.0	12	17
SDC151	51.0	51.0	M10x12	12	10	15	5.0	12	17
SDC154	51.0	51.0	M10x12	12	7.5	5	15	5	12
SDC256	63.5	63.5	M10x12	15	15	15	15	7.5	15

SPECIFICATION

RATED VOLTAGE 250V
 LINE FREQUENCY DC TO 50Hz
 AMBIENT TEMPERATURE -25°C TO 85°C
 EARTH LEAKAGE CURRENT 0.44mA
 TEST VOLTAGE 2.0KV DC

ELECTRICAL SCHEMATIC




ONLY TYPES 101 AND 151 ARE COLOUR CODED

DrgNo SDC-GS

TITLE SDC CYLINDRICAL CAN FILTER WITH STUD

ALL DIMENSIONS IN MM
 ANGLES IN DECIMAL DEGREES

ROXBURGH EMC



ISSUE 1

GENERAL SPECIFICATION
 FOR SDC

CUSTOMER

REFERENCE

Aprvd Date 10/03/03

Aprvd By JRT

Drwn by SW

Scale: NTS

Sheet 1 / 1