


Surface Mount Resistor Kit

1206 Case Size



RoHS
Compliant

Specifications Table


Type	Power Rating	Resistance Tolerance	Nominal Resistance
MC 1206	0.125W (1/8W)	±5%	10Ω

Ratings:

Type	MC 1206
Power Rating	0.125W (1/8W)
Rated Current(Jumper)	2A
Max. Overload Current(Jumper)	10A
Max. Working Voltage	500V
Max. Overload Voltage	200V
Dielectric Withstanding Voltage	400V
Temperature Range	-55°C +155°C
Ambient Temperature	+70°C

Power Rating:

Resistors shall have a power rating based on continuous load operation at an ambient temperature of 70°C . For temperature in excess of 70°C , The load shall be derate as shown in figure.



Surface Mount Resistor Kit


1206 Case Size




Nominal Resistance:

Effective figures of nominal resistance shall be in accordance with E-24 and E-96 series
E-96 series for 1 % and E-24 series for 2 % and 5 %

Construction:



Power Rating and Dimensions:



Dimension :

Type	Dimension (mm)				
	$L \pm 0.15$	$W +0.15 / -0.10$	$H \pm 0.1$	$l1 \pm 0.2$	$l2 \pm 0.2$
MC 1206	3.1	1.55	0.55	0.45	0.45

Power Rating :

Type	Power Rating	Tolerance	Resistance	Standard Series
MC 1206	0.125W (1/8W)	Jumper	< 50mΩ	E-12
		±5	10Ω ~ 1MΩ	

Surface Mount Resistor Kit

1206 Case Size



Performance Specification :

Characteristics	Limits	Test Methods (JIS C 5201-1)
Insulation resistance	1,000 MΩ or more	Apply 500V DC between protective coating and termination for 1 min, then measure
Dielectric withstanding voltage	No evidence of flashover mechanical damage, arcing or insulation break down	Apply 300V AC between protective coating and termination for 1 minute
Temperature coefficient	1Ω - 10Ω : ± 400 PPM/°C 11Ω - 100Ω : ± 200 PPM/°C >100Ω : ± 100 PPM/°C	Natural resistance change per temp. degree centigrade. $\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (PPM/°C)}$ R ₁ : Resistance value at room temperature (t ₁) R ₂ : Resistance value at room temp. plus 100°C (t ₂)
Short time overload	Resistance change rate is ± (2.0% + 0.1Ω) Max.	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds
Solderability	95 % coverage Min.	Test temperature of solder : 245 ± 3°C Dwell time in solder : 2 ~ 3 seconds
Soldering temp. Reference	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95 % coverage Min.)	<p><u>Wave soldering condition:</u> (2 cycles Max.) Pre-heat : 100°C to 120°C, 30 ±5 sec. Suggestion solder temp.: 235°C to 255°C, 10 sec. (Max.) Peak temp.: 260°C</p> <p><u>Reflow soldering condition:</u> (2 cycles Max.) Pre-heat : 150°C to 180°C, 90°C to 120 sec. Suggestion solder temp.: 235°C to 255°C, 20 to 40 sec. Peak temp.: 260°C</p> <p><u>Hand soldering condition:</u> The soldering iron tip temperature should be less than 300°C and maximum contract time should be 5 sec.</p>

Surface Mount Resistor Kit


1206 Case Size



Characteristics	Limits	Test Methods (JIS C 5201-1)															
Soldering Heat	Resistance change rate is: $\pm(1\% +0.05\Omega)$ Max.	Dip the resistor into a solder bath having a temperature of $260^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and hold it for 10 ± 1 seconds.															
Temperature cycling	Resistance change rate is $\pm(1\% +0.05\Omega)$ Max.	Resistance change after continuous 5 cycles for duty cycle specified below :															
		<table border="1"> <thead> <tr> <th>Step</th> <th>Temperature</th> <th>Time</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>$-55^{\circ}\text{C} \pm 3^{\circ}\text{C}$</td> <td>30 mins</td> </tr> <tr> <td>2</td> <td>Room temp.</td> <td>10 to 15 mins</td> </tr> <tr> <td>3</td> <td>$+155^{\circ}\text{C} \pm 2^{\circ}\text{C}$</td> <td>30 mins</td> </tr> <tr> <td>4</td> <td>Room temp.</td> <td>10 to 15 mins</td> </tr> </tbody> </table>	Step	Temperature	Time	1	$-55^{\circ}\text{C} \pm 3^{\circ}\text{C}$	30 mins	2	Room temp.	10 to 15 mins	3	$+155^{\circ}\text{C} \pm 2^{\circ}\text{C}$	30 mins	4	Room temp.	10 to 15 mins
		Step	Temperature	Time													
		1	$-55^{\circ}\text{C} \pm 3^{\circ}\text{C}$	30 mins													
		2	Room temp.	10 to 15 mins													
3	$+155^{\circ}\text{C} \pm 2^{\circ}\text{C}$	30 mins															
4	Room temp.	10 to 15 mins															
Load life in humidity	Resistance change rate is $\pm(3\% +0.1\Omega)$ Max.	Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity chamber controlled at $40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ and 90 to 95 % relative humidity															
Load Life	Resistance change rate is $\pm(3\% +0.1\Omega)$ Max.	Permanent resistance change after 1,000 hours operating at RCWV, with duty cycle of (1.5 hours"on", 0.5 hour "off") at $70^{\circ}\text{C} \pm 2^{\circ}\text{C}$ ambient															
Terminal bending	Resistance change rate is $\pm(1\% +0.05\Omega)$ Max.	Twist of Test Board : Y/X = 5/90mm for 10 seconds															

Kit resistors:

Insert for Chip Kit



Dimensions : Millimetres

www.element14.com
www.farnell.com
www.newark.com




Surface Mount Resistor Kit

1206 Case Size



Album for Chip Kit:



Dimensions : Millimetres

Chip Kit Resistors:

Product : MC Kit (1206) +/-5%
 E12 Series = 75 values (0R&10R to 1M)
 Quantity : 100pcs per value
 Total Qty : 7,500pcs.

NO.	Value
1	0E
2	1R0
3	1R2
4	1R5
5	1R8
6	2R2
7	2R7
8	3R3
9	3R9
10	4R7

NO.	Value
11	5R6
12	6R8
13	8R2
14	10R
15	12R
16	15R
17	18R
18	22R
19	27R
20	33R

NO.	Value
21	39R
22	47R
23	56R
24	68R
25	75R
26	82R
27	100R
28	120R
29	150R
30	180R

NO.	Value
31	220R
32	270R
33	330R
34	390R
35	470R
36	560R
37	680R
38	820R
39	1K
40	1K2

Surface Mount Resistor Kit

1206 Case Size



NO.	Value
41	1K5
42	1K8
43	2K2
44	2K7
45	3K3
46	3K9
47	4K7
48	5K6
49	6K8
50	8K2

NO.	Value
51	10K
52	12K
53	15K
54	18K
55	22K
56	27K
57	33K
58	39K
59	47K
60	56K

NO.	Value
61	68K
62	82K
63	100K
64	120K
65	150K
66	180K
67	220K
68	270K
69	330K
70	390K

NO.	Value
71	470K
72	560K
73	680K
74	820K
75	1M

Part Number Table

Description	Part Number
Resistor Kit, 1206, E12, 5%	MC1206W8JE012KIT

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

