



**SEMISTOP<sup>®</sup> 2**

## Bridge Rectifier

### SK100B

Target Data

### Features

- Compact design
- One screw mounting
- Heat transfer and insulation through direct copper bonded aluminium oxide ceramic (DCB)
- Up 1600V reverse voltage
- High surge current
- Glass passivated diode chips
- UL recognized, file no. E 63 532


### Typical Applications

- Input rectifier for power supplies
- Rectifier





1)  $V_F$ ,  $V_{(TO)}$ ,  $r_T$  = chip level value

$V_{RSM}$ V	$V_{RRM}$ , $V_{DRM}$ V	$I_D = 51$ A (full conduction) ( $T_s = 80$ °C)
900	800	SK100B08
1300	1200	SK100B12
1700	1600	SK100B16



Symbol	Conditions	Values	Units
$I_D$	$T_s = 80$ °C	100	A
$I_{FSM}$	$T_{vj} = 25$ °C; 10 ms $T_{vj} = 150$ °C; 10 ms	1000 890	A A
$i^2t$	$T_{vj} = 25$ °C; 8,3...10 ms $T_{vj} = 125$ °C; 8,3...10 ms	5000 3960	A <sup>2</sup> s A <sup>2</sup> s
$V_F$	$T_{vj} = 25$ °C; $I_F = 40$ A	max. 1,21	V
$V_{(TO)}$	$T_{vj} = 125$ °C	max. 0,83	V
$r_T$	$T_{vj} = 125$ °C	max. 3,9	mΩ
$I_{RD}$	$T_{vj} = 150$ °C; $V_{DD} = V_{DRM}$ ; $V_{RD} = V_{RRM}$	max. 1,1	mA mA
$R_{th(f-s)}$	per diode per module	1 0,25	K/W K/W
$T_{solder}$	terminals, 10s	260	°C
$T_{vj}$		-40...+150	°C
$T_{stg}$		-40...+125	°C
$V_{isol}$	a. c. 50 Hz; r.m.s.; 1 s / 1 min.	3000 ( 2500 )	V
$M_s$	mounting torque to heatsink	2	Nm
$M_t$			
m	approx. weight	19	g
Case	SEMISTOP <sup>®</sup> 2	T 6	



B



Dimensions in mm



Case T97

B

Case T97 (Suggested hole diameter, in the PCB, for solder pins and plastic mounting pins = 2mm)

This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.