

Multimeter



Specifications:

Basic Functions	Range		Best Accuracy
Insulation Resistance Measurement	50V	0.1MΩ~50MΩ	
	100V	0.1MΩ~100MΩ	
	250V	0.2MΩ~99.9MΩ	
		100MΩ~250MΩ	
	500V	0.5MΩ~99.9MΩ	±(3%+5)
		100MΩ~500MΩ	±(3%+5)
	1,000V	4MΩ~99.9MΩ	±(3%+5)
		100MΩ~600MΩ	±(3%+5)
100MΩ~999MΩ			
1GΩ~2GΩ			
DC Voltage Measurement	60mV/600mV/6V/60V/600V/1,000V		±(0.09%+6)
AC Voltage Measurement	6V/60V/600V/1,000V		±(1%+3)
DC Current Measurement	60mA/600mA		±(1%+2)
AC Current Measurement	60mA/600mA		±(1.5%+2)
Resistance Measurement	600Ω/6KΩ/60KΩ/600KΩ/6MΩ/40MΩ		±(0.9%+2)
Capacitance Measurement	10nF/100nF/1μF/10μF/100μF		±(3%+5)
Frequency Measurement	60Hz/600Hz/6KHz/60KHz/600KHz/1MHz		±(0.1%+3)
Temperature Testing	-40°C to 537°C		
	-40°F to 998°F		

Special Functions:

Display Count		6,000
Auto Ranging		√
True RMS		√
Diode		√
Auto Power Off		√
Continuity Buzzer		√



Multimeter



Specifications:

Basic Functions	Range	Best Accuracy
Low Battery Display		√
Data Hold		√
Min/Max Mode		√
Data Logging		99
Display Backlight		√
Full Icon Display		√
Sleep Mode		√
Memory Zeroing		√

General Characteristics:

Power LCD	1.5V Alkaline Batteries (LR6) × 6
Size Product	81mm × 46mm
Colour	Orange and Grey
Product Net Weight	505g
Product Size	96.7mm × 202.8mm × 46 mm
Standard Accessories	Batteries, Test Lead, Alligator Clip, Carrying Bag
Standard Individual Packing	Gift Box, English Manual

Part Number Table

Description	Part Number
Multimeter, Digital, Handheld, 3 3/4Digit	72-2555

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

