

# Data Sheet

## SP044xxVBNN

Page 1/4


P/N

ASP044xx

xx=number of poles

2013/12/05

### Illustration



see enlarged drawing at the end of the document

### Product specification

- spring clamp terminal block, pluggable
- centerline 3.81 mm, direction of connection vertical 0°
- color black
- eccentric lever, wire entry uncodeable side parallel to plug direction
- Connection data

**CRIUS** V / A 150 / 10

**SEV** 2.5 kV / 3 / IEC 61984

# Data Sheet

## SP044xxVBNN

### Technical Data

#### General Data

min. number of poles	2		
max. number of poles	12		
Insulating material class	CTI 400		
clearance/creepage dist.	2.6 mm		
protection category	IP 20		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	320 V	320 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

#### Connection data

 V / A	150 / 10		
--	----------	--	--

	2.5 kV / 3 / IEC 61984		
--	------------------------	--	--

#### Material

insulating material	PA46		
flammability class	V0		

#### Climatic properties

upper limit temperature	105 °C		
lower limit temperature	-40 °C		

#### General

Tolerance	ISO 2768 -mH		
-----------	--------------	--	--



# Data Sheet

## SP044xxVBNN

Page 3/4

P/N

ASP044xx

xx=number of poles

2013/12/05

### Matching Part

P/N	Product name
311901	PR044xxHBBN Typ 190
311911	PR044xxVBBN Typ 191

### Accessories

P/N	Product name
700025-01-9	700025



# Data Sheet

## SP044xxVBNN

Page 4/4

P/N


ASP044xx

xx=number of poles

2013/12/05

### Illustration

Drawing



$$L = (\text{pole size} - 1) \times \text{centerline} + 4 [0.157]$$