




# JIS Duplex Thermocouple Sockets



*'Suitable for industrial applications'*

- Duplex (2-channel) standard connector that accepts solid, round plug pins
- Bodies supplied coloured black with spacer in JIS colour coding
- Rugged glass filled polyester bodies
- Suitable for industrial applications
- Available in Thermocouple types K, J
- For Types K, J contacts are made from true Thermocouple alloys
- Contacts are polarised to prevent incorrect connection
- Colour coded in accordance with JIS specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (JIS)	+Positive (alloy type)	-Negative (alloy type)	Labfacility Code	Farnell Code
K	Blue	+Nickel Chromium	-Nickel Alloy	JS-K-FD	234-7208
J	Yellow	+Iron	-Copper Nickel	JS-J-FD	234-7207



FAR064/0613 JIS Duplex Thermocouple Sockets

### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com