

# Fiber Optic - 10/100BaseT to 100BaseFX-SC Media Converter, 2km, 1300nm

MODEL NUMBER: N784-001-SC



### Highlights

- Convert UTP Ethernet to Fiber
- Supports Auto MDI/MDI-X
- Half or Full Duplex Operation
- Auto-Senses 10/100

### Applications

- Remote network nodes that are beyond the 100 meter distance limitation of UTP

### Package Includes

- 10/100 Media Converter, UTP - SC
- AC-DC Power Adapter ( 100-240V )
- Owner's Manual

### Description

Tripp Lite's N784-001-SC 10/100 Media Converter, is an economical way to extend the distance ( up to 2Km ) of network nodes by converting Cat5/6 UTP cables to Fiber Optic. The Media Converter features automatic MDI/MDI-X configuration, and the UTP port senses the network speed automatically as well. Dip switches allow half or full duplex operation on the fiber port. Power supplied by either AC-DC adapter, or USB connection ( switch selectable ). Tripp Lite

### Features

- Connect 10BaseT/100BaseT UTP Ethernet to 100BaseFX Fiber Ethernet
- Auto MDI/MDI-X
- UTP port auto-senses network speed
- Switch selectable half or full duplex operation on the fiber port
- Fiber lengths up to 2Km
- 2 Power Choices - AC-DC Adapter or USB
- 5 LED Function lights
- Uses 62.5/125 or 50/125 Multimode cable
- 3.75"L x 2.75"W x 1"H
- Wavelength: 1310nm
- Supports Link Fault Pass-through (LFP) for easy tracing of network link failures

## Specifications

General Info	
RoHS	Y
<b>OVERVIEW</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Chromebook Compatible	No
Model Type	Converters
<b>CONNECTIONS</b>	
Connector A	RJ45 (FEMALE)
Connector B	SC (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.