

Specifications

Output

socket:	Standard USB, type A, female	
voltage:	5 V DC $\pm 5\%$	
max. current:	2.1 A	continuous
auto cut off:	≤ 30 mA	(if the output current is lower than 30mA, the output will be switched off automatically)
safety functions:	protection against external short circuit, overload and deep discharge	

Input

socket:	Micro USB, female	
voltage:	5 V DC $\pm 5\%$	
charge current:	1000 mA	$\pm 10\%$
charge time:	12...13 h	

Indicators

charge/battery status:	5 LEDs (blue)	show the charge state of the internal battery in 20% steps - while charge is in progress - when pressing the charge state test button
charge end:		all 5 LEDs light permanently when the internal battery is fully charged

Internal Battery

cell type:	LiCoO ₂	Lithium Polymer
size:	customized	(prismatic cells)
number of cells:	2	
configuration:	1S2P	
nominal voltage:	3.7 V	
capacity:	10400 mAh (2 x 5200mAh)	
energy:	38.5 Wh	
life time expectance: (C>60% of min. capacity)	≥ 500 cycles	

Temperature range

operating temperature:	- 10...50 °C
storage temperature:	- 10...30 °C (recommended)

Mechanical specifications



length L1:	160 ± 2 mm
width W1:	50 ± 1 mm
height H1:	22 ± 1 mm
weight (device only):	305 ± 10 g

Housing

material:	aluminum, anodized
colour:	black

Accessories:

micro USB to USB cable



cable length: 550mm
colour: black



ANSMANN Specifications for model:

ANSMANN Powerbank Model 10.4 (10400mAh)

data sheet no. / part no.

1700-0028





supplier no.


703572

author / date

TG / 18.06.2014

Printing:



	ANSMANN Specifications for model:	ANSMANN Powerbank Model 10.4 (10400mAh)
	data sheet no. / part no.	1700-0028
	supplier no.	703572
	author / date	TG / 18.06.2014

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice