Product data sheet Characteristics

XMLG001D21

pressure sensor XMLG - 0..1 bar - G 1/4A (male) - 24 V - 4..20 mA - set of 1



Main

Commercial Status	Commercialised
Range of product	OsiSense XM
Product or component type	Electronic pressure sensors
Pressure sensor type	Pressure transmitter
Pressure sensor name	XMLG
Pressure sensor size	1 bar
Fluid connection type	G 1/4A (male) conforming to ISO 228
Controlled fluid	Fresh water (0125 °C) Hydraulic oil (-15125 °C) Corrosive fluid (-15125 °C) Air (-15125 °C)
Type of output signal	Analogue
Analogue output function	420 mA, 2 wires
Electrical connection	3 pins 1 male connector M12
[Us] rated supply voltage	12/24 V DC, voltage limits: 833 V
Quantity per set	Set of 1
Type of packing	Individual
Diameter	22.8 mm

Complementary

Complementary	
Pressure setting range	01 bar
Maximum permissible accidental pressure	2.7 bar
Destruction pressure	3 bar
Local display	Without
Electrical circuit type	Control circuit
Current consumption	< 20 mA
Materials in contact with fluid	Ceramic FPM PPS Stainless steel type AISI 303
Operating position	Any position
Protection type	Load short-circuit Reverse polarity
Surge withstand	500 kV (12 Ohm) conforming to EN/IEC 61000-4-5 1 kV (42 Ohm) conforming to EN/IEC 61000-4-5
[Uimp] rated impulse withstand voltage	0.5 kV
Response time on output	< 2 ms
Drift of the sensitivity	+/- 0.015 % of measuring range/°C
Drift of the zero point	+/- 0.015 % of measuring range/°C
Measurement accuracy	+/- 0.3 % of the measuring range
Repeat accuracy	+/- 0.1 % of the measuring range
Mechanical durability	>= 10000000 cycles
Product weight	0.095 kg
Height	72 mm

Environment

Standards	CE EN 50081-1
	EN 50082-2
	EN 61000-6-2
	EN/IEC 60947-1
	EN/IEC 60947-5-1
Product certifications	CSA
	UL
Protective treatment	TC
Ambient air temperature for operation	-1585 °C
Ambient air temperature for storage	-4085 °C
Vibration resistance	20 gn (f = 92000 Hz) conforming to EN/IEC 60028-2-6
Shock resistance	25 gn for 11 ms conforming to EN/IEC 60068-2-27
Resistance to electrostatic discharge	8 kV (on contact) conforming to EN/IEC 61000-4-2
	15 kV (in air) conforming to EN/IEC 61000-4-2
Resistance to electromagnetic fields	200 V/m (801000 Hz) conforming to EN/IEC 61000-4-3
Resistance to fast transients	4 kV conforming to EN/IEC 61000-4-4
Resistance to conducted disturbances, induced by radio frequency fields	30 V (0.1580 Hz) conforming to EN/IEC 61000-4-6
Resistance to magnetic fields	30 A/m (50 Hz) conforming to EN/IEC 61000-4-8
IP degree of protection	IP67 conforming to EN/IEC 60529
	IP66 conforming to EN/IEC 60529
NEMA degree of protection	NEMA 4


Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0627 - Schneider Electric declaration of conformity



XMLG001D21

Dimensions



Product data sheet Connections and Schema

XMLG001D21

Wiring Diagram

2-Wire Technique (4-20 mA)



Product data sheet Performance Curves

XMLG001D21

Output Curves

