



[+ View More](#)

PRODUCT NUMBER: N06575008

Honeywell plastic cartridge P3

The P3 cartridge is part of the wide range of cartridges offered to protect against many hazardous gases, vapors and/or particulates in many applications. The Honeywell range provides high quality and a cost-effective protection. The cartridges of Honeywell range are tested against standard EN143.

Honeywell

Overview

Reference Number

N06575008

Product Type

Respiratory Protection

Range

Reusable APR

Line

Filter

Brand

Honeywell

Brand formerly known as

NORTH

Industry

- Agriculture
- Automotive and Part Manufacturer
- Aviation
- Building and Construction
- Chemical Industries
- Foundry
- General Industry
- Glass Industries
- Green Spaces
- Industrial Cleaning
- Iron and steel industry
- Laboratory
- Maintenance
- Medical and Pharmaceutical
- Metal steel
- Paper Industries
- Ship Building
- Textile Industries
- Utilities
- Water treatment
- Welding
- Wood Industries

Product Use

Controls before use

Users must:

- Ensure that the level of protection offered by the respirator is sufficient for the type and concentration of contaminant(s) in the work area.
- Respect the shelf life figuring on the filter.
- Check the seal points.

Feature

Lower profile and lightweight

Benefit

Optimal comfort

Feature

Low profile

Benefit

Do not obstruct the field of vision

Feature

Threaded connector

Benefit

Easy to attach

Feature

Small opening

Benefit

Easy check up

Features & Benefits

Filters Cartridges

Standard

EN143

Protection Type

Particulate

Connection Type

Other

Connection Type Other

N series

Protection Level

P3

Material

ABS - fiber glass paper

Technical Description

Certifications

 E.C. Declaration of Conformity

EC Category PPE

3

Quality Assurance

ISO 9001 / 2000

EC Certificate Number

0252

EC Attestation

 EC Attestation

EC Attestation Number

0252

Certifications

- EN 143

Literature & Documents

 E.C. Declaration of Conformity

Class 1 Honeywell cartridges

http://www.honeywellsafety.com/supplementary/documents_and_downloads/respiratory_pr

We're sorry, there are no images available at this time.

Additional Information

User Manual

User instructions Honeywell Class 1 cartridges - multilingual

Maintenance

Life Cycle

6 years

Storage Information

Filters should be stored in their original packaging in a cool, dry, non contaminated atmosphere. Storage under conditions other than those specified by the manufacturer may affect the shelf life.

Temperature range of storage conditions: -10°C/+40°C

Maximum humidity of storage conditions: 90% RH

Care Instructions

Conditions of use (temperature range, maximum humidity, etc.) :

Temperature range : -10°C/+40°C

Honeywell plastic cartridge P3 - N06575008

Maximum humidity : 90% RH

Restrictions of use :

In an explosive atmosphere.

- If the concentration of oxygen is less than 19.5% by volume or in an oxygen enriched environment.
- If the package unsealed or damaged.

© Honeywell International Inc.