



1



Model 15RT SHOWN

APPLICATION:
With ammeters, energy management systems, and instrumentation.

FREQUENCY:
50-400 Hz.

INSULATION LEVEL:
600 Volts, 10 kV BIL full wave.

Terminals are brass studs No. 8-32 with one flatwasher, lockwasher and regular nut.

Flexible leads are UL 1015 105°C CSA approved. #16 AWG 24" long.

Non-standard length to be specified. SFT case style also available as SFL with leads.


Approximate weight 0.9 lbs.

CATALOG NUMBER	CURRENT RATIO	ACCURACY AT 60 Hz	BURDEN VA at 60 Hz	DIM "A"	CATALOG NUMBER	CURRENT RATIO	ACCURACY AT 60 Hz	BURDEN VA at 60 Hz	DIM "A"
14**-500	50:5	±1.5%	2.5	0.50	16**-500	50:5	±2%	1.5	1.25
14**-600	60:5	±1.5%	2.5		16**-600	60:5	±2%	1.5	
14**-750	75:5	±1.5%	2.5		16**-750	75:5	±2%	3.0	
14**-800	80:5	±1.0%	2.5		16**-800	80:5	±2%	3.0	
14**-101	100:5	±1.0%	3.0		16**-101	100:5	±1%	3.0	
15**-500	50:5	±1.5%	2.0	0.94	16**-121	120:5	±1%	4.0	
15**-600	60:5	±1.5%	2.0		16**-1250	125:5	±1%	5.0	
15**-750	75:5	±1.5%	2.5		16**-151	150:5	±1%	6.0	
15**-800	80:5	±1.0%	2.0		16**-1750	175:5	±1%	7.0	
15**-101	100:5	±1.0%	2.0		16**-201	200:5	±1%	8.0	
15**-121	120:5	±1.0%	3.0		16**-251	250:5	±1%	10	
15**-1250	125:5	±1.0%	4.0		16**-301	300:5	±1%	10	
15**-151	150:5	±1.0%	5.0		16**-401	400:5	±1%	15	
15**-1750	175:5	±1.0%	10						
15**-201	200:5	±1.0%	12.5						


**Note: When ordering, prefix Cat No. with model designation required i.e. 14RL-600, 15SFT-151, 16RT-151, etc.

Model 14, 15, 16


RBT Style




RT Style




RBL Style



RL Style



SFT Style



USA, Canada, Asia, Latin America

Tel: +1-800-547-8629

Fax: +1-905-201-2455

e-mail: sales.multilin@ge.com

Europe, Middle East, Africa

Tel: +34-94-485-88-00

Fax: +34-94-485-88-45

e-mail: gmultilin.euro@ge.com

1