

TAA-Compliant SmartPro 120V 1kVA 800W Line-Interactive Sine Wave UPS, 1U Rackmount, SNMPWEBCARD Option, USB, DB9 Serial

MODEL NUMBER: **SM1000RM1UTAA**



Description

Tripp Lite SM1000RM1UTAA 1000VA / 1kVA / 800 watt line interactive, sine wave UPS system offers complete power protection for critical network applications in a highly efficient 1U total rack/tower configuration. Simultaneous-use network management interfaces include USB, RS-232 and optional SNMP/Web accessory card. Line interactive voltage regulation, network-grade surge suppression and long-lasting sine wave AC output during blackouts make this UPS ideal for advanced networking applications in datacenters, computer rooms and network closets.

Features

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- Tripp Lite SM1000RM1UTAA 1kVA / 1000VA / 800 watt line interactive UPS
- 1U rack/tower compatible form factor
- Included mounting brackets support 2 and 4 post rackmount installation; Optional [4POSTRAILKIT1U](#) is available for additional support
- NEMA 5-15P input; 6 5-15R output receptacles
- Installed depth of only 16.75 in. / 42.5cm
- Sine wave output in both AC and battery backup modes
- Line Interactive UPS provides Automatic Voltage Regulation / AVR to maintain 120V nominal output during brownouts to 83V and overvoltages to 147V without using battery power
- Full load efficiency rating of 99% saves energy and ensures cool operating temperatures
- Integrated 2 bank switched PDU enables remote outlet management for load shedding or remote reboot of individual devices
- PowerAlert monitoring software offers detailed site power and UPS updates with support for safe auto-shutdown of connected systems as UPS batteries become depleted
- Includes Free PowerAlert monitoring software packages; PowerAlert LOCAL for desktops and small business networks, PowerAlert NSA(Network Shutdown Agent) for larger networks and PowerAlert NMS(Network Management System) for monitoring up to 250 SNMP-enabled UPS, PDU and other

Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 1kVA / 1000VA / 800W line interactive 1U rackmount UPS, Sine Wave
- 120V output, Corrects brownouts and overvoltages from 83V to 147V
- 0.8 Power Factor, Front panel status LEDs
- 99% line-mode efficiency, 2 switched load banks
- USB, RS232, EPO and slot for [SNMPWEBCARD](#) option
- 120V NEMA 5-15P input, 6 NEMA 5-15R outlets
- **This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment**

Package Includes

- SM1000RM1UTAA UPS System
- Mounting hardware
- Cabling for USB & DB9 monitoring and EPO switching
- PowerAlert unattended shutdown and UPS/Power monitoring software
- Instruction manual



networking devices

- Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via built-in RS-232 and USB interfaces
- Optional [SNMPWEBCARD](#) offers communications and control via secure remote web and network interfaces
- 3 stage metered LEDs offer current monitoring and battery charge level
- Mains power and voltage regulation LEDs offer at-a-glance power status information
- Front panel switches support self-test and alarm cancel functions
- Field replaceable, hot-swappable internal UPS batteries

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1000
Output kVA Capacity (kVA)	1
Output Watt Capacity (Watts)	800
Power Factor	0.8
Nominal Output Voltage(s) Supported	120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-21%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) 5-15R
Load Management Receptacles	Two switchable single-outlet 5-15R load banks
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
INPUT	
Rated input current (Maximum Load)	9.0A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
Recommended Electrical Service	15A 120V
Input Cord Length (ft.)	10
Input Cord Length (m)	3
Input Phase	Single-Phase
BATTERY	



Full Load Runtime (min.)	4 min. (800w)
Half Load Runtime (min.)	14 min. (400w)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Internal UPS Replacement Battery Cartridge	RBC69-1U
Battery Access	Front panel battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
Expandable Runtime	No
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 83 and 107 are boosted by 14%
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure, overload and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	450 joules
UPS Dataline Suppression	1 line TEL/DSL or Ethernet
EMI / RFI AC Noise Suppression	Yes
AC Suppression Response Time	Instantaneous
PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; 2 post 19 inch rackmount
Included Mounting Accessory Description	Included mounting brackets support 2 and 4 post rackmount installation; Optional 4POSTRAILKIT1U is available for additional support
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	1.7 x 17.5 x 16.8
UPS Power Module Dimensions (hwd, cm)	4.4 x 44.4 x 42.5
Rack Height (U Spaces)	1



UPS Power Module Weight (lbs.)	32
UPS Power Module Weight (kg)	14.5
UPS Shipping Dimensions (hwd / in.)	6.2 x 23.5 x 22.5
UPS Shipping Dimensions (hwd / cm)	15.9 x 59.7 x 57.2
Shipping Weight (lbs.)	36
Shipping Weight (kg)	16.3
Cooling Method	Fan
UPS Housing Material	Steel
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	39
AC Mode Efficiency Rating (100% Load)	94%
COMMUNICATIONS	
Communications Interface	USB; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Included
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer Time	5 milliseconds AC to DC; 1 millisecond DC to AC
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	147
SPECIAL FEATURES	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI); TAA Compliant; ENERGY STAR Qualified
WARRANTY	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>