


# LQM2HPN4R7MGC#

"#" indicates a package specification code.



< List of part numbers with package codes > LQM2HPN4R7MGCL , LQM2HPN4R7MGCB

#### Shape



# References

Packaging code	Specifications	Minimum quantity
L	180mm Embossed taping	3000
В	Packing in bulk	1000

	Mass (Typ.)	
1 piece	0.022g	

## Specifications

Inductance	$4.7\mu H \pm 20\%$
Inductance test frequency	1MHz
Rated current (Itemp) (Based on Temperature rise)	800mA
Max. of DC resistance	0.225
Avg. of DC resistance	0.18 ±25%
Self resonance frequency (min.)	25MHz
Operating temperature range	-55 ~ 125
Class of magnetic shield	Magnetic shield of ferrite

#### 🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it 's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


muRata Murata Manufacturing Co., Ltd.


URL : http://www.murata.com/


Last updated: 2015/02/17

## Chart of characteristic data (The charts below may show another part number which shares its characteristics.)


#### Inductance-Frequency characteristics (Typ.)







Inductance-Current characteristics (Typ.)



2 of 2

This PDF data has only typical specifications because there is no space for detailed specifications.

Therefore, please reviewour product specifications or consult the approval sheet for product specifications before ordering.



muRata Murata Manufacturing Co., Ltd. Last updated: 2015/02/17