
Single phase, primary switched mode power supply, Economy **PVSE 230/48-5**



Standards

Primary switched mode power supply to UL 60950, UL 508

Safety: EN 61558-2-16, EN 60950-1

EMC: EN 61204-3

Advantages

Stabilised and adjustable output voltage				
Up to 200 % real power boost for 4 seconds				
Top boost to trip conventional circuit breakers				
DC OK signalling				
Stand-by-input				
Parallel connection option				
Service-friendly spring-loaded connector system				
Optional with active inrush current limiter				

Applications

 $\ensuremath{\mathsf{Primary}}$ switched mode power supply with massive power reserves focussing on the key task of power supply.

Simplified diagram







UL/CSA 60950 recognised, UL508 listed





Single phase, primary switched mode power supply, Economy PVSE 230/48-5

Туре	PVSE 230/48-5		Туре	PVSE 230/48-5
Input		0.0	Terminal and mounting	
Input rated voltage	110 - 240 Vac	~	Connections input, (spring clamp terminal,	max. 2.5 mm ²
Input rated current (rated load)	2.5 / 1.2 Aac (110 / 230 Vac)		pluggable)	11dx. 2.5 11111
Input voltage range	85 - 264 Vac (120 - 373 Vdc)	ta	Connections output, (spring clamp terminal,	max. 2.5 mm ²
Rated frequency range	44 Hz - 66 Hz / 0 Hz	Mechanical data	pluggable) Connections signalling, (spring clamp terminal,	
Starting current limiter	<8 A, active		pluggable)	max. 0.5 mm ²
Input fuse internal	6.3 A (slow-blow)	io.	Mounting position	vertical
Recommended back-up fuse (circuit breaker)	10 A, 16 A, characteristics B, C	an	Fixing method	DIN Rail system TH 35
Harmonic correction	active	낭	Measures and weights	
Mains buffering	24 / 24 ms (110 / 230 Vac)	/e	Weight	1.30 kg
Transient surge voltage protection	Varistor	2	Weight	1.30 Kg
Output				
Output rated voltage	48 Vdc ±1 %		\sim	>
Output voltage range	33 - 52 Vdc			
Resistance to reverse feed max.	63 Vdc			£11 ∥
Output rated current	5.00 A			
Parallel connection	Yes			
Power Boost	10 A / 4 s (7.5 A / 8 s)			
Overload behaviour	Constant current		127.0	
max. Power loss idling/nominal load	7.4 / 21.6 W			
Serial operation	Yes			
Efficiency	typ. 91 %			
Ripple factor	typ. 70 mVss			
Top Boost	30 A / 25 ms			
Signaling				
Stand-by-input	Yes			12.5
Power Good (DC OK)	LED green, LED red		· · ·	-
Potential free signal contact	Yes			
Standards				
Classification	Primary switched mode power supply			
Approvals				
Approvals	cURus, cULus			
	conus, collus			
Environment				
Storage temperature	-25° C to +85° C			
Derating	-3 %/K > +50° C,			
0	-1.5 %/Vac < 110 Vac -10° C to +70° C			
Ambient temperature	-TO C M +/O_C			
Safety and protection				
Safety class	I, with PE connection			
Protection index	IP 20			
Accessory				
Connector for signalling	PV-CON (optional)			
Side DIN Rail mounting	PV-TS35M (optional)			
Direct screw fastening plate for lateral mounting	PV-WB2 (optional)			
Order numbers				
	PVSE 230/48-5			

6.0

