



JFM

JFM Magnifiers - Luxo's newest high-quality illuminated magnifiers. Like the WAVE+Plus Magnifiers, manufactured in Europe, JFM Magnifiers are an ideal medium-duty magnifiers for inspection, assembly and rework applications.



- 5" diameter 3-diopter (1.75X) or 5-diopter (2.25X) optical quality white crown glass lenses
- 22-Watt circline fluorescent lamp
- Instant-on switch
- Minimum Clearance Bracket allows for almost zero clearance (approx. 1/4" (6.35mm))
- Adjustable neck moves the magnifier head vertically and horizontally for complete flexibility
- Lamp diffuser cover
- 45" reach external spring arm
- Electronic ballast produces 15% greater light output
- UL/CUL listed
- 5 year warranty

RELATED PRODUCTS



IFM



KFM



Wave+Plus Magnifiers

CODES

JFM MAGNIFIERS - 3-DIOPTER

Article Number	Light Source	Watt	Weight	Arm Length	Mount	Ctn. Colors
16113LG	Circline Fluorescent	22W	8.8	45.0/1143	Edge mount 1	■

JFM MAGNIFIERS - 5-DIOPTER

Article Number	Light Source	Watt	Weight	Arm Length	Mount	Ctn. Colors
16115LG	Circline Fluorescent	22W	8.8	45.0/1143	Edge mount 1	■

LENS DATA

Code	Diopter primary	Total Magnification (x)	Total Magnification (%)	Focal Length (mm)
16113LG	3.00	1.8	175	333.3
16115LG	5.00	2.3	225	200.0

ACCESSORIES

DESIGNATION

10-Diopter Swing Away Lens	50206
34" Floor Stand	50036
Flush/Surface Mount Bushing	31639
C Surface Mount	50005
B Wall Mount	50003
A Edge Mount Bracket	60001