


HFT-A 25.4/12.7

Article number: 305-25400



HFT-A conforms to major standards used in all Defence industries.



This flexible heat shrink tubing has many excellent properties including fast shrinking, easy handling, good mechanical strength and resistance against chemicals and solvents. It is UL and CSA approved, easy to print on and available in a wide range of colours and internal diameters up to 4 inches (101.6mm).

This high performance thin wall tubing is used extensively for electrical and mechanical protection. It is also well proven for sleeve marking to identify wiring circuits. It shrinks uniformly to form a permanent insulation covering. The transparent version is used for bundling and cable protection where visual inspection is required. It is often used as a see through protective sleeve over cable markers.

UL Listed (US and Canada)

TRUE

Base Data

Colour

Black (BK)

Short Description

HFT-A is coloured and self extinguishing. HFT-B is transparent and halogen free.

Shrink Ratio

2:1

Size (imperial)

1"

Size (metric)

25.4/12.7

Logistic and Packaging

Carton Quantity

50

EAN code HT

4031026272894

Package Content

25 m

Quantity of Europallet

3000

Quantity per

M

Weight (kg) (Metric)

5.474 kg

Material and Specifications

Designation as per VG-Norm

VG 95343 T05 A 010 A

Dielectric Strength (metric)	20 kV/mm according to IEC 60684 P2
Flammability	Self extinguishing
Insulation Class	B (VDE 0530)
Material	Polyolefin, cross-linked (POX)
Material Shortcut	POX
Minimum Shrink Temperature (Metric)	+100 °C
Operating Temperature (Metric)	-55 °C to +135 °C
ROHS Conformity	TRUE
Specification	DEF STAN 59-97/3, SAE - AMS - DTL-23053 / 5C, CSA, NFF 00-608, UL224, DNV, VG 95343
Product Dimensions	
Length L (Metric)	50
Longitudinal change after shrinkage	-5% max.
Recovered Diameter D (metric)	12.7
Supplied Diameter D (metric)	25.4
Wall Thickness WT (Metric)	0.9