



BOSCH

Invented for life

Power tools for trade & industry

Product data sheet



Cordless inspection camera

GOS 10,8 V-LI

Quick problem analysis in hard-to-reach areas

The most important data

Display resolution	320 x 240 px
Display size	2,7
Battery voltage	10,8 V



Part number: 0 601 241 007

from **GBP 185,00***

[> More product information](#)


** Recommended retail price excluding VAT*

Technical data

Battery voltage	10,8 V
Display size	2,7 "
Display resolution	320 x 240 px
Diameter of camera head	9,5 mm
Number of LED lighting stages	9
Runtime with one battery charge	7–15 h

**Power tools for trade & industry****Advantages:**

- Realistic image rendering on 2.7" LCD display with high resolution
- Bright Power LED for optimum illumination in dark areas
- Extra-long, waterproof camera cable (91 cm) with small camera head for a flexible range of applications
- Video-out interface for external image transfer
- Bosch Premium lithium-ion technology for longer lifetime

**Prices / Scope of delivery**

Part number	0 601 241 071	0 601 241 007
1 x 1.5 Ah Li-Ion battery 2 607 336 761	✓	-
1/2 L-BOXX inlay for charger 1 600 A00 2VN	✓	-
1/2 L-BOXX inlay for tool 1 600 A00 2VP	✓	✓
AL 1130 CV quick charger (ET no. 2 607 225 135)	✓	-
Cardboard	-	✓
GOS camera cable, 9.5 mm diameter, 91 cm long 2 610 014 568	✓	✓
L-BOXX 102 1 600 A00 1RP	✓	-
Magnet, hook, mirror 2 610 014 565	✓	✓
Video-out cable	✓	✓
Price (Recommended retail price excluding VAT)	GBP 225,00	GBP 185,00