



## Main

Range	TeSys
Product name	TeSys CAD
Product or component type	Control relay
Device short name	CAD
Contactor application	Control circuit
Utilisation category	AC-14 AC-15 DC-13
Pole contact composition	5 NO
[Ue] rated operational voltage	<= 690 V AC 25...400 Hz
Control circuit type	DC standard
Control circuit voltage	24 V DC

## Complementary

[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
[Ith] conventional free air thermal current	10 A at <= 60 °C
Irms rated making capacity	250 A DC conforming to IEC 60947-5-1 140 A AC conforming to IEC 60947-5-1
[Icw] rated short-time withstand current	140 A 100 ms 120 A 500 ms 100 A 1 s
Associated fuse rating	10 A gG conforming to IEC 60947-5-1
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1 600 V certifications CSA 600 V certifications UL
Mounting support	Plate Rail
Connections - terminals	Screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end Screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end Screw clamp terminals 2 cable(s) 1...2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end
Tightening torque	1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2
Control circuit voltage limits	0.1...0.25 U <sub>c</sub> drop-out 0.7...1.25 U <sub>c</sub> operational
Operating time	16...24 ms coil de-energisation and NO opening 53...72 ms coil energisation and NO closing
Mechanical durability	30 Mcycles
Operating rate	180 cyc/mn
Time constant	28 ms
Inrush power in W	5.4 W at 20 °C
Hold-in power consumption in W	5.4 W at 20 °C

Minimum switching voltage	17 V
Minimum switching current	5 mA
Non-overlap time	1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact)
Insulation resistance	> 10 MOhm
Height	77 mm
Width	45 mm
Depth	93 mm
Product weight	0.58 kg

## Environment

Standards	BS 4794 EN 60947-5 IEC 60947-5-1 NF C 63-140 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x front face conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without derating in temperature
Mechanical robustness	Vibrations control relay closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations control relay open 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks control relay closed 15 Gn for 11 ms IEC 60068-2-27 Shocks control relay open 10 Gn for 11 ms IEC 60068-2-27

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0627 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Download Product Environmental</a>
Product end of life instructions	Need no specific recycling operations