

118-04800



Article Number: 118-04800

Outside Serrated Cable Tie, 5.7" Long, 30lb Tensile Strength, PA66HS, Black, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 118-04800

Type T30ROS

Color Black (BK)

- Features and Benefits**
- Outside serrations minimize damage to cables, while still providing high tensile strength and low insertion force.
 - Contour style head design provides additional space in constrained areas.
 - Heat stabilized material provides excellent resistance to high heat exposures.

Product Description HellermannTyton outside serrated cable ties are designed with a smooth inside surface to help minimize indentation or damage to wire and cable insulation, while offering high tensile strength and low insertion force. The contour style head takes up less space than traditional style cable ties making it ideal for space constrained areas. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Outside Serrated Cable Tie, 5.7" Long, 30lb Tensile Strength, PA66HS, Black, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 30.0 lbs

Minimum Tensile Strength (Metric) 135.0 N

Length L (Imperial) 5.7 "

Length L (Metric) 145.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.13 "

Width W (Metric) 3.4 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.6 mm

Bundle Diameter Max. (Imperial) 1.4 "

Bundle Diameter Max. (Metric) 35.0 mm

Thickness T (Imperial) 0.05 "

Cable Tie Head Length (Imperial) 0.22 "

Cable Tie Head Width (Imperial) 0.24 "

Thickness T (Metric) 1.2 mm

Logistics and Packaging

Quantity Per bag
Package Quantity (Metric) 100 Pieces
Carton Quantity 10000 Pieces
Weight (Metric) 0.7 kg

Material and Specifications

Material Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut PA66HS
Flammability UL94 V2
Halogenfree Yes
Operating Temperature -40°F to +221°F (-40°C to +105°C)
ROHS Compliant Yes
Certification/Specification PAN6481