



ELECTRONICS, INC.

44 FARRAND STREET  
BLOOMFIELD, NJ 07003  
(973) 748-5089  
http://www.nteinc.com

## NTE569 Silicon Rectifier Fast Switching, Soft Recovery

**Features:**

- Fast Recovery
- Diffused Junction
- High Surge Capability

**Absolute Maximum Ratings:**

Peak Recurrent and Non-Recurrent Reverse Voltage,  $V_{RRM}$  ..... 600V  
 Forward Current (R Load,  $T_A = +50^\circ\text{C}$ ),  $I_{F(AV)}$  ..... 3A  
 Recurrent Peak Forward Current,  $I_{FRM}$  ..... 15A  
 Peak Forward Surge Current (10ms,  $T_A = +25^\circ\text{C}$ ),  $I_{FSM}$  ..... 100A  
 Maximum Reverse Recovery Time ( $I_F = 0.5\text{A}$  to  $I_R = 1\text{A}$  with  $I_{rr} = 0.25\text{A}$ ),  $t_{rr}$  ..... 250ns  
 Maximum Operating Junction Temperature  $T_J$  .....  $+150^\circ\text{C}$   
 Storage Temperature Range,  $T_{stg}$  .....  $-65^\circ$  to  $+150^\circ\text{C}$   
 Lead Temperature (During Soldering, 4mm from case, 3.5sec),  $T_L$  .....  $+350^\circ\text{C}$   
 Maximum Thermal Resistance, Junction-to-Case,  $R_{thJC}$  .....  $30^\circ\text{C/W}$

**Electrical Characteristics:** ( $T_A = +25^\circ\text{C}$  unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Maximum Forward Voltage Drop	$V_F$	$I_F = 3\text{A}$	-	-	1.3	V
Maximum Reverse Current	$I_R$	$V_{RRM} = 600\text{V}$	-	-	10	$\mu\text{A}$

