



# Querstromventilator mit Kapillarkeilzunge



## Crossflow fan with perforated guide vane

# QK 10

Einphasen / Single phase

### Leistungsdaten

#### Performance data



Ventilator-Typ Fan type	U V	f Hz	P <sub>1</sub> W	I A	n min <sup>-1</sup>	C μF	q <sub>v</sub> m <sup>3</sup> /h	L <sub>WA</sub> dB(A)	R / P <sub>R</sub> Ω / W	Min.pressung Min. pressure
QK10A-4EM.38.CD ①	230	50 60	70 90	0,36 0,4	1260 1310	2	680 700	63 68	1200/40	
QK10A-4EM.48.CD ②	230	50 60	80 90	0,35 0,45	1140 1230	2	820 880	62 66	1200/40	
QK10A-4EM.48.CF ③	230	50 60	100 140	0,45 0,61	1330 1510	3	890 1010	63 68	750/40	
QK10A-4EM.68.CD ④	230	50 60	80 90	0,36 0,41	1040 1060	2	1040 1060	64 66	1200/40	
QK10A-4EM.68.CF ⑤	230	50 60	120 150	0,5 0,64	1270 1370	3	1190 1290	65 69	750/40	
QK10A-4EM.78.CF ⑥	230	50 60	120 150	0,52 0,63	1250 1310	3	1360 1420	64 68	750/40	
QK10A-4EM.78.CH ⑦	230	50 60	130 180	0,6 0,82	1280 1350	4	1400 1480	64 67	300/80	
QK10A-4EM.98.CF ⑧	230	50 60	130 150	0,54 0,64	1200 1230	3	1540 1570	65 66	750/40	
QK10A-4EM.98.CH ⑨	230	50 60	140 170	0,63 0,8	1220 1260	4	1600 1670	65 68	300/80	
QK10A-4EM.B8.CH ⑩	230	50	140	0,6	1110	4	1720	64	300/80	