


Capacitor, Tantalum, SMD, Polymer, Molded, Low ESR, Non-Combustible, 22 uF, 3528, +/-20% Tol, 16 VDC (105C)



General Information

Supplier:	KEMET
Application:	Low ESR
Sub Application:	(NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, Low ESR, Non-Combustible
Construction:	Standard Chip-Polymer
Body Type:	SMD Chip
Footprint:	3528
Weight:	94.85 mg
RoHS:	Yes

Dimensions (mm)

Symbol	Dimension	Tolerance
L	3.5	+/-0.2
W	2.8	+/-0.2
H	1.9	+/-0.1
F	2.2	+/-0.1
S	0.8	+/-0.3
B	0.4	+/-0.15
X	0.1	+/-0.1
P	0.5	REF
R	1	REF
T	0.13	REF
A	1.9	MIN

Specifications

Capacitance:	22 uF
Tolerance:	+/-20%
Voltage:	16 VDC (105C)
Temperature Range:	-55/+105C
Current/Ripple Current:	1200 mAmps (100kHz 45C)
Current/Ripple Current:	840 mAmps (85C)
Current/Ripple Current:	570 mAmps (105C)
Resistance/ESR:	90 mOhms (100kHz 25C)
Failure Rate:	N/A
Leakage Current:	35.2 uA
Dissipation Factor:	8%

Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	2000