

175REF

Article Number: 590-01751

Rite-On Self-Laminating Label Refill, .75" X .75" X 3.0", Vinyl, White, 90/RL



Download spec sheet

## Base Data

Local Order Number 175REF

Type 175REF

Color White (WH)

- Features and Benefits**
- Compact to easily fit in pants or shirt pockets.
  - Dispenser can be reloaded over and over, making it cost effective to use.
  - Dispenser edge allows easy removal of label liner.
  - Dispenser protects labels from dirt and moisture before use, extending the life and quality of the labels.

Color Marking Field White (WH)

**Product Description** HellermannTyton's Rite-On Markers are made from a flexible vinyl film and used to mark wire and cable. The self-laminating labels have a clear tail which seals the legend under clear vinyl, maintaining the quality of the labels. The Rite-On markers are packaged in a reusable dispenser made from high impact plastic which is resistant to oils and grease.

Mounting method Identification ETIM Pasting / Stick

Short Description Rite-On Self-Laminating Label Refill, .75" X .75" X 3.0", Vinyl, White, 90/RL

## Product Dimensions

Length L (Imperial) 0.75 "

Length L (Metric) 19.05 mm

Fixation Method Pasting / Stick

Self adhesive (Yes/No) Yes

Variant Roller form

Width W (Imperial) 0.75 "

Width W (Metric) 19.05 mm

Height H (Imperial) 0.75 "

Height H (Metric) 19.05 mm

Height H2 (Imperial) 3.0 "

Height H2 (Metric) 76.20 mm

Bundle Diameter Min. (Imperial) 0.33 "

Bundle Diameter Min. (Metric) 8.32 mm

Bundle Diameter Max. (Imperial) 0.7 "

Bundle Diameter Max. (Metric) 17.78 mm

Outside Diameter Min. (Imperial) 0.33 "

Outside Diameter Min. (Metric) 8.38 mm

Outside Diameter Max. (Imperial) 0.7 "

Outside Diameter Max. (Metric) 17.78 mm

## Logistics and Packaging

---

**Quantity Per** pack  
**Package Quantity** 90  
**Package Quantity (Metric)** 90  
**Carton Quantity** 1 Pieces

## Material and Specifications

---

**Material** Type 100, Vinyl (PVC), white (WH), self laminating  
**Material Shortcut** 100  
**Adhesive** Acrylic  
**Adhesive Shortcut** Acrylic  
**Adhesive Operating Temperature** -51°F to +200°F (-46°C to +93°C)  
**Operating Temperature** -51°F to +200°F (-46°C to +93°C)  
**ROHS Compliant** Yes