

Economy Wall Mount Cabinet *RB-FW Series*



Features

- Constructed in light duty 16-gauge steel.
- Includes two (2) pairs of EIA-310-D compliant 19 inch square hole mounting rails.
 - Starter pack of (25) M6 screws, cage nuts and washers included.
 - For 10-32 hardware see the **1421CNABK Series**.
- Rails are adjustable.
- Includes one (1) tempered glass reversible front door.
- Includes one (1) pair of locking removable side panels.
- Front and side of frame includes venting for air flow.
- Rear cable access.
- Provision for optional fans on top panel.
- Ships un-assembled - some assembly required.
- Finished in black powder paint.
- Tested to 130 lbs of equipment load capacity.
- RoHS Compliant.



Part of the Rack Basics® line of economy rack solutions.

Accessories

- Horizontal Ring Cable Manager
- Horizontal Lacing Strip
- Outlet Strips
- Mounting Hardware
- Universal Rack Shelf
- Cable Lacing Bar
- Grill Fan Kits

Part No.	Overall Dimensions			Mounting Dimensions			Usable	Rack Units	Replaces
	Height	Width	Depth	Height	Width	Depth	Depth		Part No.
RB-FW6	14.65	23.62	23.62	10.50	19.00	16.93	22.87	6U	WMC1901023BK2
RB-FW9	19.90	23.62	23.62	15.75	19.00	16.93	22.87	9U	WMC1901523BK2
RB-FW12	25.15	23.62	23.62	21.00	19.00	16.93	22.87	12U	WMC1902123BK2
RB-FW15	30.40	23.62	23.62	26.25	19.00	16.93	22.87	15U	WMC1902123BK2

Note: Usable depth is the furthest depth equipment can be mounted in the cabinet.

Data subject to change without notice