


# 1.9kW Single-Phase Metered PDU, 120V Outlets (14 5-15/20R), L5-20P/5-20P adapter, 0U Vertical, 36-in.

MODEL NUMBER: PDUMV20-36



## Description

Tripp Lite single phase Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital display. Enables visual monitoring of PDU load levels to prevent overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

## Features

- 20A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA L5-20P input plug with 15ft / 4.6m line cord and 5-20P adapter
- 0U 36-in. / 91.4cm vertical rackmount format installs using no rack spaces
- 14 NEMA 5-15/20R outlets
- Includes 20A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

## Highlights

- Metered single phase 120V 20A 0U 36-in. / 91.4cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15ft / 4.6m cord with NEMA L5-20P plug and 5-20P adapter
- 14 NEMA 5-15/20R outlets
- Toolless button mount and bolt-down bracket installation hardware included

## Applications

- Ideal means of powering networking equipment in datacenters, computer rooms and network closets

## Package Includes

- PDUMV20-36 Metered Vertical PDU
- (1) L5-20P to 5-20P plug adapter
- Mounting hardware and spare mounting buttons
- Instruction manual with warranty information

## Specifications

OVERVIEW	
PDU Type	Metered
OUTPUT	
Output Capacity Details	1.9kW (120V input), 2.0kW (127V input), 1.6kW (100V input); 20A maximum (Agency de-rated to 16A continuous)



Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15/20R
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	20A
Outlet Type	NEMA 5-15/20R
Individual Outlet Switching	No
<b>INPUT</b>	
PDU Input Voltage	100; 120; 127
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.6
Input Phase	Single-Phase
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LEDs	Digital ammeter display
Switches	Lighted on/off switch with integrated transparent safety cover
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	2.6 x 38.93 x 6.78
Shipping Dimensions (hwd / cm)	6.6 x 98.9 x 17.22
Shipping Weight (lbs.)	3.79
Shipping Weight (kg)	1.72
Unit Dimensions (hwd / in.)	36 x 1.75 x 1.25
Unit Dimensions (hwd / cm)	91.4 x 4.45 x 3.18
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.45
Material of Construction	Aluminum
Form Factors Supported	Vertical
PDU Form Factor	Vertical (0U)
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL60950-1 (USA), UL/CSA60950-1 (Canada), NOM (Mexico), FCC Class A (Emissions), RoHS Compliant



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>