

# 34 42 130 ESD

## Precision Electronics Gripping Pliers ESD



- for very precise assembly work, e.g. in electronics and fine mechanics
- for gripping, holding and bending
- electrically discharging handles - dissipative
- smoothly ground gripping surfaces, edges finely rounded
- approx. 20% lighter than conventional electronics pliers
- bolted joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- smooth-running double spring for a gentle and even opening
- ergonomically optimised multi- component handles
- forged from chrome vanadium ball-bearing steel
  - Style:flat, wide jaws
  - Style:with precision laser cut cross-shaping



### The subtle difference

KNIPEX precision electronics pliers are made of high-quality ball bearing steel and processed with the highest degree of care. Each opening movement is gentle and even without backlash. Each work step proceeds reliably and precisely. This makes work much easier for professionals.



### ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

<b>Article No.</b>	34 42 130 ESD
<b>EAN</b>	4003773080299
<b>Style</b>	4
<b>Pliers</b>	burnished
<b>Head</b>	polished
<b>Handles</b>	with multi-component grips
<b>B mm</b>	21,90
<b>A mm</b>	11,20
<b>D mm</b>	6,50
<b>E mm</b>	1,40
<b>F mm</b>	3,50
<b>Length mm</b>	130
<b>Net weight g</b>	61

technical change and errors excepted