

## 2-Port HDMI over Cat5/Cat6 Active Extender, Remote Unit

MODEL NUMBER: **B126-2A0**



### Description

The B126-2A0 is a receiver unit that is used with the B126-002 and B126-004 transmitter units. It extends a 1080p (60Hz) signal to two monitors up to 150 ft. away using Cat5e/6 cable, and then splitting the signal out to 2 x HDMI outputs. To achieve maximum distance and resolution, use 24Awg Solid Wire Cat5e/6 cable. (Tripp Lite's N202-Series) It features a built-in Equalization control for adjustment of the video image. Supports 24-bit True Color (8-bits per channel), HDCP, 3D, and both stereo audio and 7.1 channel surround sound audio (7.1 channel surround sound signal will be Multi-Channel or PCM).

Installation is simple. Connect the transmitter unit to an HDMI source using a Tripp Lite P568-Series HDMI cable (not included). Connect the receiver unit to a display using a Tripp Lite P568-Series HDMI cable (not included). Finally, connect the receiver to the RJ45 port on the transmitter using a single Cat5e/6 cable.

- A 1080p (60Hz) signal can be transmitted up to 150 ft.
- A 1080i (60Hz) signal can be transmitted up to 200 ft.
- A 3D signal can be transmitted up to 125 ft.

Further extend the signal range or add more displays by using a Tripp Lite Remote Repeater unit:

- Add up to three repeaters, with a receiver unit located at the end of the installation, for a total of 4 displays.
- A 1080p (60Hz) signal can be extended up to 125 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080p (60Hz) signal can be extended up to 500 ft..
- A 1080i (60Hz) signal can be extended up to 175 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080i (60Hz) signal can be extended up to 700 ft..
- A 3D signal can be extended up to 100 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 3D signal can be extended up to 400 ft..

### Features

- HDMI Receiver, splitting to 2 x HDMI outputs

### Highlights

- Receiver unit splits out to 2 x HDMI ports for two TV connection
- For use with the B126-002 and B126-004 transmitter units
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- HDCP and 3D compatible
- Compatible with both stereo audio and 7.1 channel surround sound audio (7.1 channel surround sound signal will be Multi-Channel or PCM)
- Supports 24-bit True Color (8-bits per channel)
- Can further expand the range and number of monitors by adding repeaters
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- B126-1A0 HDMI Over Cat5 Active Extender Remote Unit
- Screwdriver for adjustment of Equalization
- Mounting hardware
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's manual



- For use with B126-002 and B126-004 transmitter units.
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, is required to achieve maximum distance and resolution.
- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source and monitor.
- HDCP and 3D compatible.
- Compatible with both stereo audio and 7.1 channel surround sound audio (7.1 channel surround sound signal will be Multi-Channel or PCM).
- Supports 24-bit True Color (8-bits per channel).
- Can further expand the range and number of monitors by adding repeaters.
- Connect up to three repeaters, with a receiver unit located at the end of the installation, for a total of 5 displays.
- A 1080p (60Hz) signal can be extended up to 125 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080p (60Hz) signal can be extended up to 500 ft..
- A 1080i (60Hz) signal can be extended up to 175 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080i (60Hz) signal can be extended up to 700 ft..
- A 3D signal can be extended up to 100 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 3D signal can be extended up to 400 ft..
- Features a built-in Equalization control for adjustment of the video image.
- Compatible with all operating systems.
- Plug and play; No drivers required.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

## Specifications

OVERVIEW	
Display Style	Extender
Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Unit Dimensions (hwd / in.)	1 x 2.5 x 3.6
Unit Dimensions (hwd / cm)	2.54 x 6.35 x 9.14
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	HDMI (FEMALE)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Ports	2
<b>SPECIAL FEATURES</b>	
Chromebook Compatible	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>