



REVISIONS				
LTR	DESCRIPTION	DATE	DWN	APVD



Test Label

P/N	EFN110-xxxM-STST		
S/N	Client Numbers(P/O)-Serial Number -N		
ST/ST:62.5/125;[Length]M			
DUPLX FIBER OPTIC CABLE			
INSERTION LOSS			
A1	dB	B1	dB
A2	dB	B2	dB

ST CONNECTOR SET



N0	PART NAME
1	DUST CAP
2	MM 127 FERRULE
3	FLANGE
4	SPRING
5	COUPLING NUT
6	WASHER
7	CRIMP
8	BOOT (BLACK)

Specification

- Cable Marking:**BLACK BOX CORPORATION GUARANTEED FOR LIFE (724) 746-5500-MULTIMODE FIBER PATCH CABLE-ZIPCORD MMF-62.5/125 OFNR-(UL) E223839 xx/xxxx xxxxM
- Fiber:**Multimode 62.5/125um Optical Fiber
- Fiber cord:**PVC(OFNR CLASS) 2.9\*6.0mm ,Color Orange
- Operating wavelength:**850nm
- Insertion Loss:**≤ 0.3dB

DWN	Yangli	17Mar2006	NAME 2.9*6.0mm Orange PVC ST-ST 62.5/125 Patchcord			
CHK		17Mar2006				
APVD		17Mar2006				
UNIT: mm			DRAWING NO. EFN110-xxxM-STST			
BLACK BOX			SCALE NTS	SHEET 1	OF 1	REV 0