



OK434/12 FV

12 pole red-brown polyamide PA6.6, with 25% glass fibre reinforced pillar terminal block 12mm pitch 57a 450v



SPECIFICATION

| | |
|---------------------------------------|--|
| Number of Poles | 12 |
| Terminal Material | OT58 nickel plated |
| Body Material | Polyamide PA6.6, with 25% glass fibre reinforced |
| Colour | Red-brown |
| Glow Wire Resistance Test Temp | GWT750°C in 2 sec (EN60695-2-11) |
| Max Conductor Size (Sq mm) | 10 |
| Max Current (A) | 57 |
| Max Voltage (V) | 450 |
| Working Temperature | 150 |
| Pitch (mm) | 12 |
| Height (mm) | 20.2 |
| Width (mm) | 23.2 |
| Length (mm) | 140.3 |
| Diameter (mm) | 4.4 |
| Terminal Screw Material | White zinc plated steel |