



Main

Range	TeSys
Product name	TeSys CAK
Product or component type	Control relay
Device short name	CA2K
Contactor application	Control circuit
Utilisation category	AC-15 DC-13
Pole contact composition	2 NO + 2 NC
[Ue] rated operational voltage	≤ 690 V ≤ 400 Hz
Control circuit type	AC 50/60 Hz
Control circuit voltage	110 V AC 50/60 Hz

Complementary

[Ith] conventional free air thermal current	10 A at ≤ 50 °C
Irms rated making capacity	110 A conforming to IEC 60947
Associated fuse rating	10 A gG conforming to VDE 0660 10 A gG conforming to IEC 60947
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 690 V conforming to BS 5424 750 V conforming to VDE 0110 group C 690 V conforming to IEC 60947
Mounting support	Plate Rail
Connections - terminals	Screw clamp terminals 2 cable(s) 0.34...1.5 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable(s) 0.34...1.5 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable(s) 0.75...4 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable(s) 0.75...4 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable(s) 1.5...4 mm ² - cable stiffness: solid Screw clamp terminals 1 cable(s) 1.5...4 mm ² - cable stiffness: solid
Tightening torque	1.3 N.m - on screw clamp terminals - with screwdriver Philips No 2 6 mm 1.3 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
Control circuit voltage limits	0.8...1.15 U _c at 50 °C operational 0.2...0.75 U _c at 50 °C drop-out
Operating time	5...15 ms coil energisation and NC opening 15...25 ms coil de-energisation and NC closing 10...20 ms coil energisation and NO closing 10...20 ms coil de-energisation and NO opening
Mechanical durability	10 Mcycles
Operating rate	10000 cyc/h
Immunity to microbreaks	2 ms
Inrush power in VA	30 VA at 20 °C
Hold-in power consumption in VA	4.5 VA at 20 °C
Heat dissipation	1.3 W
Minimum switching voltage	17 V
Minimum switching current	5 mA

Non overlap distance	0.5 mm
Insulation resistance	> 10 MOhm
Height	58 mm
Width	45 mm
Depth	57 mm
Product weight	0.18 kg

Environment

Standards	BS 5424 IEC 60947 NF C 63-140 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-50...80 °C
Operating altitude	2000 m without derating in temperature
Flame retardance	Requirement 2 conforming to NF F 16-102 Requirement 2 conforming to NF F 16-101 V1 conforming to UL 94
Mechanical robustness	Shocks contactor closed 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor open 10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor open 2 Gn, 5...300 Hz IEC 60068-2-6

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0640 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations