


EVEREADY 276



Industry Standard Dimensions



Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

Designation: ANSI / NEDA-1603, IEC-6F100

Battery Voltage: 9.0 Volts

Average Weight: 245 grams (8.6 oz.)

Volume: 261 cubic centimeters (15.9 cubic inch)


Average Capacity: 5000 mAh to 0.8 volts/cell
(Rated at 25 mA continuous drain at 21°C)

Cells: Thirty six No. 117 - Six parallel strings of six in series.

Jacket: Paper

TYPICAL DISCHARGE CURVE

Simulated Test @ 21°C (70°F)



Simulated Application Test Estimated Average Service at 21°C (70°F)

Schedule:	Typical Drains at 7.2V (milliamperes)	Load (ohms)	Cutoff Voltage				
			4.2V	4.8V	5.4V	6.0V	6.6V 7.2V
4 hours/day	14	510	335	333	310	2.66	2.10

Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. Inc. - All Rights Reserved