


CAMBLOCK PLUS

5mm Pitch Low Profile Screw Terminal Blocks

CTBP5000

- 2 & 3 pole interlocking
- Test probe facility
- Moulded in grey UL94-V0 flame retardant PA66
- 1.5mm² (22-14AWG)
- Wire protector terminals
- Guided pin alignment
- Anti solder wicking terminal
-  approved



SPECIFICATION

Rating	UL=16A/250V, VDE=24A/250V
Insulation resistance	500MΩ/500V
Withstand Voltage	AC2000V/1min
Contact Resistance	20mΩ (max)
Working Temperature	-40°C to 105+°C
Mouldings	UL94-V0 Flame retardant PA66
Pin/Terminal	Tin plated brass
Wire Protector	Phosphor bronze, nickel plated
Screw/Torque	M2.5 Steel, zinc plated 0.4Nm
Recommended PCB hole size	ø1.2mm

TYPE NO.	POLES	LENGTH
CTBP5000/2	2	10mm
CTBP5000/3	3	15mm
CTBP5000/4	4	20mm
CTBP5000/5	5	25mm
CTBP5000/6	6	30mm
CTBP5000/7	7	35mm
CTBP5000/8	8	40mm
CTBP5000/9	9	45mm
CTBP5000/10	10	50mm
CTBP5000/11	11	55mm
CTBP5000/12	12	60mm

