

## REL50R0L4



**Article Number:** 115-00502

**Releasable Cable Tie, 5.5" Long, 50 lb Tensile Strength, PA66, Black, 200/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** REL50R0L4

**Type** REL50R

**Color** Black (BK)

**Features and Benefits**

- Special design offers a release feature for quick and easy access to wire bundles.
- Head design provides high tensile strength even after repeated use; providing additional longevity.

**Product Description** HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Releasable Cable Tie, 5.5" Long, 50 lb Tensile Strength, PA66, Black, 200/pkg

### Product Dimensions

**Minimum Tensile Strength (Imperial)** 50.0 lbs

**Minimum Tensile Strength (Metric)** 225.0 N

**Length L (Imperial)** 5.5 "

**Length L (Metric)** 140.0 mm

**Fixation Method** None

**Identification Plate Position** none

**Releasable Closure** Yes

**Tie Closure** plastic pawl

**Variant** Outside Serrated

**Width W (Imperial)** 0.29 "

**Width W (Metric)** 7.4 mm

**Cable Tie Width Max. (Imperial)** 0.42 "

**Cable Tie Width Max. (Metric)** 10.7 mm

**Height H2 (Imperial)** 0.31 "

**Height H2 (Metric)** 7.8 mm

**Bundle Diameter Min. (Imperial)** 0.08 "

**Bundle Diameter Min. (Metric)** 2.0 mm

**Bundle Diameter Max. (Imperial)** 1.4 "

**Bundle Diameter Max. (Metric)** 35.0 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 200

Carton Quantity 5000

## Material and Specifications

---

|                              |                                  |
|------------------------------|----------------------------------|
| <b>Material</b>              | Polyamide 6.6 (PA66)             |
| <b>Material Shortcut</b>     | PA66                             |
| <b>Flammability</b>          | UL94 V2                          |
| <b>Operating Temperature</b> | -40°F to +185°F (-40°C to +85°C) |
| <b>ROHS Compliant</b>        | Yes                              |