

## T120S0HSH4



Article Number: 111-12821

Heavy Duty Cable Tie, 8.9" Long, 120lb Tensile Strength, PA66HS, Black, 500/pkg



Download spec sheet

### Base Data

Local Order Number T120S0HSH4

Type T120S

Color Black (BK)

**Features and Benefits**

- Heat stabilized heavy duty cable ties provide excellent resistance to high heat exposures.
- Head design provides high tensile strength with very low insertion force.
- Bent tail ensures a quick and simple installation.

**Product Description** HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Heavy Duty Cable Tie, 8.9" Long, 120lb Tensile Strength, PA66HS, Black, 500/pkg

### Product Dimensions

Minimum Tensile Strength (Imperial) 120.0 lbs

Minimum Tensile Strength (Metric) 535.0 N

Length L (Imperial) 8.9 "

Length L (Metric) 225.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.3 "

Width W (Metric) 7.6 mm

Bundle Diameter Min. (Imperial) 0.2 "

Bundle Diameter Min. (Metric) 5.0 mm

Bundle Diameter Max. (Imperial) 2.2 "

Bundle Diameter Max. (Metric) 55.0 mm

### Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 500 Pieces

Carton Quantity 1000

### Material and Specifications

---

<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Material Shortcut</b>	PA66HS
<b>Flammability</b>	UL94 V2
<b>Halogenfree</b>	Yes
<b>Operating Temperature</b>	-40°F to +257°F (-40°C to +125°C)
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL-ZODZ2.E64139
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes