

# 9012GBW2

pressure switch 9012G - adjustable scale - 2  
thresholds - 20 to 675 psig



Product availability: Stock - Normally stocked in distribution facility

Price\*: 595.00 USD



## Main

Commercial Status	Commercialised
Range of product	9012G
Pressure sensor type	Electromechanical pressure switch
Pressure sensor name	9012G
Pressure sensor size	675 psi
Maximum pressure	2000 psi
Contacts type and composition	NC-NO, SPDT-DB, Form Z, snap action, silver nickel contacts
Controlled fluid	Non-corrosive gas Air Non-corrosive liquids Hydraulic oil (-40...250 °F)
Fluid connection type	0.25 inch 18 NPTF conforming to UL 508
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable
Local display	Without

## Complementary

Range on decreasing pressure	20...675 psi
Approx differential at mid range	27...130 psi +/- 2.5 % full scale
Cable entry	0.5 inch NPT conduit entrance
Terminal block type	4 screw terminals
Electrical connection	Screw-clamp terminals, AWG 22...12
Electrical circuit type	Control circuit
Local signalling	Without
[In] rated current	0.22 A (Ue = 125 V DC) contact code: R300 conforming to NEMA rating designation 0.27 A (Ue = 250 V DC) contact code: R300 conforming to NEMA rating designation 6 A (Ue = 120 V AC) contact code: A600 conforming to NEMA rating designation 3 A (Ue = 240 V AC) contact code: A600 conforming to NEMA rating designation
Setting	Internal
Enclosure material	Die cast aluminum alloy 380
Pressure actuator	Diaphragm (nitrile (Buna-N))
Height	5.45 in
Depth	2.63 in
Width	3.5 in
Operating position	Any position
Materials in contact with fluid	Zinc plated steel Nitrile (Buna-N)
Short circuit protection	10 A by gL (cartridge) overload and short-circuit protection
Operating rate	<= 120 cyc/mn (-10...185 °F)
Mechanical durability	5000000 cycles

Repeat accuracy	> 0...< 4 %
Product weight	3 lb(US)

## Environment

Vibration resistance	2 gn conforming to IEC 68-2-6 (f = 40...150 Hz)
Shock resistance	50 gn conforming to IEC 58-2-27
Standards	CE UL 508 CSA C22.2 No 14
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E12158 CCN NKPZ and CCN NTHT
NEMA degree of protection	NEMA 4/4X/13 conforming to UL 50
Ambient air temperature for operation	-10...185 °F

## Ordering and shipping details

Category	21522 - 9012 G INDUSTRIAL PRESSURE SWITCHES
Discount Schedule	DS1
GTIN	00785901024828
Nbr. of units in pkg.	1
Package weight(Lbs)	3.00
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 1150 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Download Product Environmental</a>
Product end of life instructions	Available <a href="#">Download End Of Life Manual</a>

## Contractual warranty

Period	18 months
--------	-----------