

Hi-Spot ES(D)63

HS ES63 240V 75W 50° GU10 SV1

0022264



Range Features

- Halogen light without the need for a transformer
- Installing and changing lamps made easier with the twist and lock GU10 and GZ10 caps
- Unique patented, computer designed spiral faceted reflector
- 100% dimmable
- For accent or decorative lighting in retail, commercial and domestic applications
- Suitable for outdoor use when protected from contact with water
- Average rated life 2500hrs



PRODUCT OVERVIEW

Lamp finish	Aluminium
Lamp shape	Reflector
Colour temperature (K)	2800
CRI (Ra)	100
Dimmable	Yes
EAN code	5410288222646
Energy class	D
Equivalent watt (W)	No
Cap/Base	GU10
Beam angle(°)	50
Type	HI-SPOT ES63 / ESD63
Watt (Nominal) (W)	75
Light colour	828 Homelight
Ordering number	0022264
Average life (Rated) (h)	2500
Luminous flux (Rated) (lm)	700
Technology	Halogen
Voltage (V)	240

DATA TABLE

General data

Average life (Nominal) (h)	2500
Control gear required	No
Lamp finish	Aluminium
Lamp shape	Reflector
Dimmable	Yes
EAN code	5410288222646

Hi-Spot ES(D)63

HS ES63 240V 75W 50° GU10 SV1

0022264

Energy class	D
Energy saving lamp	No
Fixture rating	Open
General application	Hospitality;Residential & Consumer;Retail
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-3
IEC Reference 3	IEC 60630
Intended purpose	General lighting
Cap/Base	GU10
Lamp mercury content (mg)	0
Type	HI-SPOT ES63 / ESD63
No. of switching cycles before premature failure (min)	> 10000
Ordering number	0022264

Range features

Halogen light without the need for a transformer
 Installing and changing lamps made easier with the twist and lock GU10 and GZ10 caps
 Unique patented, computer designed spiral faceted reflector
 100% dimmable
 For accent or decorative lighting in retail, commercial and domestic applications
 Suitable for outdoor use when protected from contact with water
 Average rated life 2500hrs

Product name	HS ES63 240V 75W 50° GU10 SV1
Average life (Rated) (h)	2500
Special purpose lamp	No
Starting time (max) (s)	0
Technology	Halogen
Transformer required	no
Sales pack quantity	15
Warm-up time to 60% of full light (max) (s)	Instant Full Light
E-number SE	8355955
E-number FI	4749395

Optical data

Colour temperature (K)	2800
CRI (Ra)	100
Beam angle(°)	50
Light colour	828 Homelight
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	700
Peak intensity (cd)	1000
Luminous flux (Rated) (lm)	700

Hi-Spot ES(D)63

HS ES63 240V 75W 50° GU10 SV1

0022264

Suitable for accent lighting	Yes
Beam angle (Rated) (°)	50


Electrical data

Current (A)	0.31
Equivalent watt (W)	No
kWh per 1000 hours burning time	75
Lamp power factor	1
Watt (Nominal) (W)	75
Watt (Rated) (W)	75
Voltage (V)	240

Physical data

Max. Lamp Diameter (mm) - D	64
Lamp Length (mm) - C/L	62
Single packaging type	Box/Sleeve
Weight (kg)	0.08
Lamp dimension equal to filament lamp equivalent	Yes
Designed for optimum use in non standard conditions	No
Outer package dimensions (L x W x H) (cm)	32.00 x 21.00 x 8.50
Single package dimensions (L x W x H) (cm)	6.00 x 6.00 x 6.80

TECHNICAL DRAWINGS



Hi-Spot ES(D)63

HS ES63 240V 75W 50° GU10 SV1

0022264

