


PROLINE G2 DRESS FRAME

APPLICATION

A PROLINE G2 Dress Frame provides a decorative trim when a front door or cover is not used. It is frequently used for open rack applications.

SPECIFICATIONS

- Provides a clean, finished aesthetic for open rack applications
- Snap-in design for easy, tool-free installation

FINISH

- Polyester powder paint; RAL 7035 textured light gray standard
- Custom colors available


ACCESSORIES

- 19-in. rack angles
- Rack panels
- Fixed shelf (rack mount)
- Pull-out shelf (rack mount)
- Glides (rack mount)
- Slides
- Rack angle mounted drawer
- Writing surface

BULLETIN: P40

Standard Product

Catalog Number	Fits Frame HxW
P2DF66	600x600
P2DF68	600x800
P2DF86	800x600
P2DF88	800x800
P2DF106	1000x600
P2DF108	1000x800
P2DF126	1200x600
P2DF128	1200x800
P2DF146	1400x600
P2DF148	1400x800
P2DF166	1600x600
P2DF168	1600x800
P2DF186	1800x600
P2DF188	1800x800
P2DF206	2000x600
P2DF208	2000x800
P2DF226	2200x600
P2DF228	2200x800



89129480

Model	Component	Type	Height	Width	Specialty	Catalog Number
P2	D	F	20	8	Blank	= P2DF208
PROLINE G2	Door	Blank = single door OD = double door W = window door A = side door adapter DR = disconnect right DL = disconnect left DR2 = disconnect right large cutout F = dress frame	mm 22 = 2200 20 = 2000 18 = 1800 16 = 1600 14 = 1400 12 = 1200 10 = 1000 8 = 800 6 = 600 4 = 400	mm 8 = 800 6 = 600	Blank = standard HF = EMC protected	