

Multilayer Chip Inductors for High Frequency Applications (HK series)

HK212556NJ-T



■ Features

- Item Summary
56nH±5%, 0.3A, 0805/2012 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 3000pcs

■ Products characteristics table

Inductance	56 nH ± 5 %
Case Size (EIA/JIS)	0805/2012
Rated Current (max)	0.3 A
DC Resistance (typ)	0.28 Ω
DC Resistance (max)	0.75 Ω
Q (min)	18
Q (typ)	23
LQ Measuring Frequency	100 MHz
Self Resonant Frequency (min)	800 MHz
Self Resonant Frequency (typ)	1100 MHz
Operating Temp. Range	-40 to +85 °C
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow/Wave

■ External Dimensions

Dimension L	2.0 +0.3/-0.1 mm
Dimension W	1.25 ±0.2 mm
Dimension T	1.0 +0.2/-0.3 mm
Dimension e	0.5 ±0.3 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.