

Multilayer Chip Inductors for High Frequency Applications (HK series)

HK21256N8J-T



■ Features

- Item Summary  
6.8nH±5%, 0.3A, 0805/2012 (EIA/JIS)
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping Embossed 4000pcs

■ Products characteristics table

Inductance	6.8 nH ± 5 %
Case Size (EIA/JIS)	0805/2012
Rated Current (max)	0.3 A
DC Resistance (typ)	60 mΩ
DC Resistance (max)	250 mΩ
Q (min)	15
Q (typ)	20
LQ Measuring Frequency	100 MHz
Self Resonant Frequency (min)	2800 MHz
Self Resonant Frequency (typ)	4200 MHz
Operating Temp. Range	-40 to +85 °C
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow/Wave

■ External Dimensions

Dimension L	2.0 +0.3/-0.1 mm
Dimension W	1.25 ±0.2 mm
Dimension T	0.85 ±0.2 mm
Dimension e	0.5 ±0.3 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the Date at any time without notice. Before making final selection, please check product specification.