

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0194320001

Status:

Active

Overview:

MX150L™ Industrial Sealed Connector System

Description:

MX150L™ 4 Circuit Female Receptacle for 10-12 AWG Wire

Documents:

3D Model

Packaging Specification PK-19432-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-19432-001 (PDF)

Product Literature (PDF)

Agency Certification	
CSA	LR18689
UL	E152602
General	
Product Family	Crimp Housings
Series	19432
Application	Power, Wire-to-Wire
Comments	Mat Seal Color is Yellow, Polarized to Mating Part. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector S
Overview	MX150L™ Industrial Sealed Connector System
Product Literature Order No	987650-2181
Product Name	MX150L™
UPC	822350191524
Physical	
Circuits (maximum)	4
Circuits Detail	2x2
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Net Weight	19.598/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C
Electrical	
Current - Maximum per Contact	30.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-19432-001
Product Specification	PS-19432-001
Sales Drawing	SD-19432-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/108/2014 (17 Dec

2014)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

19432 Series

Mates With

19433-0001 Male Plug

Use With

19434 Female Terminals

This document was generated on 06/09/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION