



Features

- Conductive Velostat™ container
- Ideal for static-safe storage, kitting, and in-process handling of static-sensitive assemblies and devices
- Black, injection molded container
- Size is 3.81" (Diameter) x 4.69" (Height), 9.7cm x 11.9cm
- Snug-fitting conductive lid included

SPECIFICATIONS

Physical Properties

Property	Test Method	Value
Hardness	ASTM D2240	67-71 Shore D
Maximum Temp. Exposure		180°F
Tensile Strength	ASTM D638	2800 - 3000 psi
Flex Modulus	ASTM D790	130,00 - 150,000 psi
Electrical Conductance		
Volume Conductive	ASTM D991	<500 ohms/cm
Volume Resistance	ANSI/ESD STM11.12	<1 x 10 ⁴ ohms

Chemical Resistance	Reactions
Alcohol	Resistant
Aromatic Hydrocarbons	Severe Attack
Aliphatic Hydrocarbons	Moderate Attack
Concentrated Acids	Slight Attack
Concentrated Alkalines	Slight Attack
Kerosene	Severe Attack
Keytones (Acetone)	Moderate Attack
Mineral Oil	Slight Attack
Oil & Gasoline	Moderate Attack



Made in the
United States of America

Specifications and procedures subject to change without notice

CONDUCTIVE VELOSTAT™ ROUND CONTAINER

PROTEKTIVE PAK
13520 MONTE VISTA AVENUE, CHINO, CA 91710
PHONE (909) 627-2578
ProtektivePak.com

DRAWING NUMBER
57018

DATE:
January
2016

Unless otherwise noted, tolerance is ±10%

PROTEKTIVE PAK