Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5504FE Multi-Conductor - Commercial Applications



For more Information please call

1-800-Belden1



General Description:

Security & Alarm Cable, Riser-CMR, 6-22 AWG stranded bare copper conductors with polyolefin insulation. Beldfoil® shield and PVC jacket with ripcord

insulation, belololik shield and PVC jacket wit	птрсога		
Physical Characteristics (Overall)			
Conductor AWG:			
# Conductors AWG Stranding Conductor Material			
6 22 7x30 BC - Bare Copper			
Total Number of Conductors:	6		
Insulation	·		
Insulation Material:			
Insulation Material Wall Thickness (in.)			
PP - Polypropylene 0.008			
Outer Shield			
Outer Shield Material:			
Outer Shield Trade Name Type Outer Shield Material Beldfoil® Tape Aluminum Foil-Polyester Tape w/Sh	Coverage (%)		
	lorating Pola 100		
Outer Shield Drain Wire AWG: AWG Stranding Drain Wire Conductor Material			
24 Solid TC - Tinned Copper			
Outer Jacket Outer Jacket Material:			
Outer Jacket Material Nom. Wall Thickness (in.)			
PVC - Polyvinyl Chloride 0.017			
Outer Jacket Ripcord:	Yes		
Overall Cable			
Overall Cabling Lay Length & Direction:			
Length (in.) Direction Twists (twist/ft) 2.750 Left Hand 4.400			
Overall Cabling Color Code Chart:			
Color			
Black			
Red White			
Green			
Brown			
Blue			
Overall Nominal Diameter:	0.172 in.		
Mechanical Characteristics (Overall)			
Operating Temperature Range:	-20°C To +75°C		
UL Temperature Rating:	75°C		
Bulk Cable Weight:	27.200 lbs/1000 ft.		
Max. Recommended Pulling Tension:	60.100 lbs.		
Min. Bend Radius/Minor Axis:	1.625 in.		
Applicable Specifications and Agency Compliance (Overall)			
Applicable Standards & Environmental Programs			
NEC/(UL) Specification:	CMR		
NEC Articles:	800		

Page 1 of 3 05-02-2016

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5504FE Multi-Conductor - Commercial Applications

CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
lame Test	
UL Flame Test:	UL1666 Vertical Shaft
CSA Flame Test:	FT4
uitability	
Suitability - Indoor:	Yes
lenum/Non-Plenum	
Plenum (Y/N):	No
Plenum Number:	6504FE

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft) 22.500

Nom. Capacitance Cond. to Other Conductor & Shield:

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 15.3

Max. Operating Voltage - UL:

300 V RMS

Max. Recommended Current:

Description	Current	
10C Temperature ris	2 Amps per conductor @ 25°C ambient	

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5504FE 008U1000	1,000 FT	23.000 LB	GRAY		6 #22 PP FS FRPVC
5504FE 008U500	500 FT	12.500 LB	GRAY		6 #22 PP FS FRPVC
5504FE 0081000	1,000 FT	29.000 LB	GRAY	С	6 #22 PP FS FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 08-09-2013

© 2016 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification.

Page 2 of 3

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



5504FE Multi-Conductor - Commercial Applications

Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Page 3 of 3