

Capacitor, Aluminum, 440 uF, +/-20% Tol, -55/+125C, 50 VDC@125C



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	10	+/-0.5
L	18	+/-1
S	5	+/-0.5
LLPos	19	MIN
LLNeg	15	MIN
F	0.6	+/-0.5

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag

General Information	
Supplier:	KEMET
Application:	125C Polymer
Part Type Description:	Single Ended, Polymer Aluminum
Lead Type:	Wire Leads
RoHS:	Yes

Specifications	
Capacitance:	440 uF
Voltage:	50 VDC
Tolerance:	+/-20%
Voltage:	57.5 VDC (Surge)
Life:	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Rated Temperature:	125C
Temperature Range:	-55/+125C
Leakage Current:	3.3 mA
Leakage Condition:	uAmps (2min 20C)
Dissipation Factor:	12%
Impedance Ratio -25C:	1.25
Impedance Ratio -55C:	1.25
Resistance/ESR:	28 mOhms (100kHz 20C)
Current/Ripple Current:	6.01 mAmps (100kHz 105C)
Current/Ripple Current:	3.5 mAmps (100kHz 125C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.