



Datasheet for part number CA3106E24-10SBA232

Our Catalog Part Number: CA3106E24-10S-B-A232
Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET

Product Datasheet	
Bayonet	Connector with bayonet coupling
Shell Style	Plug, straight
Endbell Style	Endbell with clamp and bushing
Gender	Socket
Shell Size	24
Contact Arrangement	24-10
Number of contacts	7 contacts size 8
Contact Type	Solder Cup
Contact Plating	Hard silver
Shielding	no
Contact Rating at +20 °C (68 °F) (Size 60/100/8)	74 A
Contact Resistance (Size 60/100/8)	1 mΩ
Operating Voltage	In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.
Insulator Resistance	Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ
Test Voltage	2000 Vrms
Air and Creepage Paths (Min)	1,1 mm
Ambient Temperature	Standard insulator material -55°/+125°C (-67/257°F)
Safety Provisions	IP67 and IP68 (1 bar pressure after 12 hrs) acc. to DIN 40 050
Salt Spray Resistance	200 hours salt spray resistant
Mating Cycles	500 min
Sep. Force per Contact (Size 60/100/8)	3,0 N
Gage	For infos on Gage please see catalog VG95234, part 1
Coupling Torque	Closing: 14 Nm max / Opening: 0,8 Nm min
Contact Retention (Size 60/100/8)	80 N
Shell Material	Aluminium alloy
Shell Plating	Zinc cobalt, black (conductive)
Insulator and Grommet Material	CR-Elastomere
Contact Material	Copper alloy
Harnessing Info: Contact Cross-Section	See assembly instruction
Harnessing Info: Insulator Diameter	See assembly instruction
Wire Stripping (Size 60/100/8)	11,8 mm
General Info	<i>All tests in accordance with VG95319 and/or if applicable with VG95210</i>