xb5avb6

blue complete pilot light Ø22 plain lens with integral LED 24V



Main

Range of product	Harmony XB5		
Product or component type	Complete pilot light		
Device short name	XB5		
Bezel material	Plastic		
Fixing collar material	Plastic		
Mounting diameter	22 mm		
Sale per indivisible quantity	1		
Shape of signaling unit head	Round		
Cap/operator or lens colour	Blue		
Operator additional information	With plain lens		
Light source	Protected LED		
Bulb base	Integral LED		
Light source colour	Blue		
[Us] rated supply voltage	24 V AC/DC, 50/60 Hz		

Complementary


Height	42 mm
Width	30 mm
Depth	54 mm
Terminals description ISO n°1	(X1-X2)PL
Product weight	0.038 kg
Resistance to high pressure washer	7000000 Pa at 55 °C,distance: 0.1 m
Connections - terminals	Screw clamp terminals : <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1 Screw clamp terminals : 1 x 0.222 x 2.5 mm² without cable end conforming to EN/IEC 60947-1
[Ui] rated insulation voltage	250 V (degree of pollution: 3) conforming to EN 60947-1
[Uimp] rated impulse withstand voltage	4 kV conforming to EN 60947-1
Signalling type	Steady
Supply voltage limits	19.230 V DC 21.626.4 V AC
Current consumption	18 mA
Service life	100000 h at rated voltage and 25 °C
Surge withstand	1 kV conforming to IEC 61000-4-5

Environment

protective treatment	TH			
ambient air temperature for storage	-4070 °C			
ambient air temperature for operation	-2570 °C			
class of protection against electric shock	Class II conforming to IEC 60536			
IP degree of protection	IP66 conforming to IEC 60529			
NEMA degree of protection	NEMA 13 NEMA 4X			
IK degree of protection	IK05 conforming to IEC 50102			
standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 UL 508 CSA C22.2 No 14			

product certifications	CSA UL listed			
vibration resistance	5 gn (f = 12500 Hz) conforming to IEC 60068-2-6			
shock resistance	50 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 30 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27			
resistance to fast transients	2 kV conforming to IEC 61000-4-4			
resistance to electromagnetic fields	10 V/m conforming to IEC 61000-4-3			
resistance to electrostatic discharge	6 kV on contact (on metal parts) conforming to IEC 61000-4-2 8 kV in free air (in insulating parts) conforming to IEC 61000-4-2			
electromagnetic emission	Class B conforming to IEC 55011			

Dimensions




e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

b: 30 mm / 1.18 in.c: 41.5 mm / 1.63 in.

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3 $_{0}^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 in. $_{0}^{+0.016}$)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

Detail of Lug Recess



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3 $_{0}^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 in. $_{0}^{+0.016}$)