

SAFETY DATA SHEET

SECTION 1: Identification

AOS Heat Sink Compound

AOS Product Code: 52022



REACH
Ready!

Manufacturer:

AOS Thermal Compounds
22 Meridian Road, Suite 6
Eatontown, New Jersey 07724
(732) 389-5514

Emergency Telephone Numbers:

Health: (732) 389-5514 9-5 EST M-F
Flammability: (732) 389-5514 9-5 EST M-F

SECTION 2: Hazard Identification

GHS Label Elements



Signal Word: WARNING

Hazard Statement(s): Skin Irritant (skin and eyes)

SECTION 3: Composition/information on ingredients

	<u>CAS Registry #</u>
Zinc Oxide	1314-13-2
00840600 # 5000P	(Trade Secret)
00840600 # 5001P	(Trade Secret)
00840600 # 5002P	(Trade Secret)

- Based on the data available to AOS, this product is not considered a hazard under OSHA Hazard Communication Standard 29 CFR1910.1200.
- The Zinc Oxide in this product is in paste form and will not pose a dust hazard.

AOS Thermal Compounds

Tel. (732)389-5514 22 Meridian Road, Suite 6, Eatontown, NJ 07724 Fax (732)389-6380

02/01/15 ♦♦♦♦ Page 1

SECTION 4: First Aid Measures

- Route of Exposure
 - Inhalation: N/A
 - Skin: Wash with soap and water
 - Eye Contact: Flush eyes with water
 - Ingestion: Consult a physician; do not induce vomiting

SECTION 5: Fire Fighting Measures

- Extinguishing Media: Foam, Carbon Dioxide, Dry Chemical
- Fire Fighting Instructions: Wear self-contained breathing apparatus for enclosed or confined areas
- Unusual Fire & Explosion Hazards: None known

SECTION 6: Accidental Release Measures

- Personal precautions – Do not ingest, protective equipment – wear gloves
- Collect product and repackage in a container.
- Dispose product in landfill as environmental precaution
- For containment and clean up use common solvents such as mineral spirits or acetone followed by soap and water

SECTION 7: Handling and Storage

- Storage temperature: Ambient
- Storage pressure: Atmospheric
- General: Keep container closed
- Avoid direct flames

SECTION 8: Exposure Controls, Personal Protection

- Control Parameters (Biological): N/A
- Appropriate Engineering controls: Gloves
- Respiratory Protection: Not necessary
- Ventilation: Under normal conditions, no special ventilation is needed
- Skin Protection: Gloves are not necessary
- Eye Protection: Safety glasses are not necessary
- Work/Hygienic Practices: Safety glasses & gloves are recommended

SECTION 9: Physical and Chemical Properties

Appearance:	White Paste	Specific Gravity:	2.7 (H ₂ O=1)
Odor:	Odorless	Vapor Pressure:	<0.1 mm Hg
Odor Threshold:	N/A	Vapor Density:	Not relevant
pH:	N/A	Relative Density:	2.4 g/cc
Melting Point/Freezing Point:	N/A	Solubility in Water:	Insoluble
Initial Boiling Point and Boiling Range:	>400°F/ >204°C	Partition coefficient/ n-octanol/water	N/A
Flash Point:	565°F/296° (COC)	Auto-ignition Temperature:	N/A
Evaporation Rate:	<0.01 (butyl acetate=1)	Decomposition Temperature:	225 °C
Flammability Limits:	LFL: Not determined UFL: Not determined	Viscosity:	870,000, 70,000 cP @ 1, 10 sec ⁻¹ shear @ 25 °C
Upper/lower Flammability Limits:	N/A		

SECTION 10: Stability and Reactivity

- Reactivity: Product is stable; hazardous polymerization will not occur.
- Chemical Stability: Inert
- Possibility of Hazardous Reactions: None known
- Materials & Conditions to Avoid: Strong oxidizing agents
- Incompatible Materials: N/A
- Hazardous Decomposition Products: None known

SECTION 11: Toxicological Information

- Route of Exposure
 - Inhalation: N/A
 - Ingestion: Consult a physician
 - Skin: Wash with soap and water
 - Eye Contact: Flush eyes with water

Symptoms related to physical, chemical and toxicological characteristics: None known

Delayed and immediate effects and also chronic effects from short and long term exposure: None known

Measures of toxicity: N/A

SECTION 12: Ecological Information

- Ecotoxicity: N/A
- Persistence and degradability: N/A
- Bioaccumulative potential: N/A
- Mobility in soil: N/A

AOS Thermal Compounds

Tel. (732)389-5514 22 Meridian Road, Suite 6, Eatontown, NJ 07724 Fax (732)389-6380

02/01/15 ♦♦♦♦ Page 3

SECTION 13: Disposal Information

- Incinerate or dispose of materials in accordance with local, state & federal regulations.

SECTION 14: Transport Information

- UN Number: N/A
- UN Proper Shipping Name: Non-Hazardous Heat Sink Compound
- Transport Hazard Class: Non-Hazardous
- Environmental Hazards (Marine Pollutant): No
- Transport in Bulk: Yes
- Special Transport Precautions: N/A
- Not a hazardous material for DOT, TDG classification, ADR/RID, IMDG, and IATA-DGR shipping.

SECTION 15: Regulatory Information

- All ingredients are on the Toxic Substances Control Act (TSCA) Inventory list or are not required to be listed. If you export this product, please ensure that the ingredients meet the inventory listing requirement of the receiving company.

SECTION 16: Other Information

- The information herein is presented in good faith and believed to be accurate as of the revision date shown above. However, no warranty, expressed or implied, is given. It is the buyer's responsibility to ensure that its activities comply with federal, state or provincial, and local laws.
- This MSDS has been updated to conform to standards set forth by the Chemical Manufacturers Association as released through the American National Standard Institute. (See ANSI Z400.1-1993)